

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219914

Luminaire Tested: **MRZ-1-REC-X-1H-L27-80-WFL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14883)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-1H-L27-80-WFL-UNV-X-STD-SFL
Description: MRZ INTEGRAL LED DOWNLIGHT
55 DEGREE WIDE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL 1
Light Source: (1) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 572.3 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.9
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 6.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219914

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-80-WFL-UNV-X-STD-SFL

Luminous Intensity Polar Plot





TEST NUMBER: P219914

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-80-WFL-UNV-X-STD-SFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	69	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	283447
5°	281558
10°	270886
15°	249773
20°	224824
25°	197992
30°	160657
35°	117450
40°	80186
45°	52819
50°	34540
55°	21935
60°	14012
65°	8756
70°	6491
75°	4194
80°	1989
85°	0



TEST NUMBER: P219914

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-80-WFL-UNV-X-STD-SFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.3	9.3
10°-20°	136.4	23.8
20°-30°	164.8	28.8
30°-40°	122.7	21.4
40°-50°	60.4	10.6
50°-60°	23.8	4.2
60°-70°	8.2	1.4
70°-80°	2.4	0.4
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	354.6	62.0
0°-40°	477.3	83.4
0°-60°	561.6	98.1
0°-90°	572.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	572.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	574	
5°	568	53
15°	489	136
25°	364	165
35°	195	123
45°	76	60
55°	26	24
65°	8	8
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P219914

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-80-WFL-UNV-X-STD-SFL

CANDELA DISTRIBUTION (FULL):

	0°
0°	574.5
2.5°	572.2
5°	568.5
7.5°	557.2
10°	540.7
12.5°	516.7
15°	489.0
17.5°	458.2
20°	428.2
22.5°	398.2
25°	363.7
27.5°	324.7
30°	282.0
32.5°	237.7
35°	195.0
37.5°	157.5
40°	124.5
42.5°	97.5
45°	75.7
47.5°	58.5
50°	45.0
52.5°	33.7
55°	25.5
57.5°	18.7
60°	14.2
62.5°	10.5
65°	7.5
67.5°	6.0
70°	4.5
72.5°	3.0
75°	2.2
77.5°	1.5
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)