

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P226100

Luminaire Tested: **MRZ-1-REC-X-1-L27-80-WFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P226100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14881)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-1-L27-80-WFL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
55 DEGREE WIDE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 1
Light Source: (1) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 253.7 lumens
Efficiency: N/A
Efficacy: 47.0 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.67
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 5.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P226100

CATALOG NUMBER: MRZ-1-REC-X-1-L27-80-WFL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P226100

CATALOG NUMBER: MRZ-1-REC-X-1-L27-80-WFL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91	89
3	104	99	94	91	103	97	93	90	95	91	89		92	90	87		90	88	86	84
4	100	93	88	85	98	92	88	84	90	86	83		88	85	82		86	84	81	80
5	96	88	83	79	94	87	83	79	86	81	78		84	80	78		83	79	77	76
6	92	84	78	75	90	83	78	74	82	77	74		80	76	73		79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70		77	73	70		76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66		73	69	66		72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63		70	66	63		69	66	63	62
10	78	69	64	61	77	69	64	60	68	63	60		67	63	60		67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	245407
5°	232130
10°	205256
15°	166209
20°	126535
25°	93634
30°	60275
35°	31802
40°	13783
45°	5094
50°	2072
55°	1118
60°	592
65°	700
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P226100

CATALOG NUMBER: MRZ-1-REC-X-1-L27-80-WFL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.9	16.9
10°-20°	89.6	35.3
20°-30°	78.1	30.8
30°-40°	34.6	13.6
40°-50°	6.8	2.7
50°-60°	1.4	0.5
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	210.6	83.0
0°-40°	245.2	96.6
0°-60°	253.4	99.9
0°-90°	253.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	253.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	497	
5°	469	43
15°	325	90
25°	172	78
35°	53	35
45°	7	7
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P226100

CATALOG NUMBER: MRZ-1-REC-X-1-L27-80-WFL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

0°	
0°	497.4
2.5°	487.4
5°	468.7
7.5°	443.2
10°	409.7
12.5°	368.9
15°	325.4
17.5°	279.9
20°	241.0
22.5°	206.8
25°	172.0
27.5°	138.5
30°	105.8
32.5°	76.3
35°	52.8
37.5°	34.1
40°	21.4
42.5°	12.1
45°	7.3
47.5°	4.6
50°	2.7
52.5°	2.0
55°	1.3
57.5°	1.3
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)