

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219751

Luminaire Tested: **MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14876)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
40 DEGREE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 4
Light Source: (1) 2700K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 919.5 lumens
Efficiency: N/A
Efficacy: 58.2 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219751

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P219751

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	88	84	80	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	75
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69
10	83	76	71	68	83	75	71	68	75	71	68	74	70	68	73	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1256638
5°	1193983
10°	1032692
15°	774553
20°	482778
25°	253683
30°	114397
35°	44269
40°	17325
45°	8722
50°	4145
55°	3097
60°	1776
65°	2101
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219751

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.5	23.9
10°-20°	409.8	44.6
20°-30°	222.3	24.2
30°-40°	53.8	5.9
40°-50°	10.2	1.1
50°-60°	2.8	0.3
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	851.6	92.6
0°-40°	905.5	98.5
0°-60°	918.4	99.9
0°-90°	919.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	919.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2547	
5°	2411	220
15°	1516	410
25°	466	222
35°	74	54
45°	12	10
55°	4	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219751

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

	0°
0°	2547.0
2.5°	2500.4
5°	2410.8
7.5°	2276.4
10°	2061.3
12.5°	1806.8
15°	1516.4
17.5°	1206.3
20°	919.5
22.5°	665.0
25°	466.0
27.5°	313.7
30°	200.8
32.5°	123.7
35°	73.5
37.5°	44.8
40°	26.9
42.5°	17.9
45°	12.5
47.5°	7.2
50°	5.4
52.5°	3.6
55°	3.6
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)