

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219720

Luminaire Tested: **MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219720  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14875)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD  
Description: MRZ INTEGRAL LED DOWNLIGHT  
40 DEGREE FLOOD OPTIC, LIGHT LEVEL 4  
Light Source: (1) 2700K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1573.2 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 15.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219720

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD

### Luminous Intensity Polar Plot





TEST NUMBER: P219720

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87	84	82	81
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77	73	71	69
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74	70	67	66
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71	67	64	63
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68	64	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1420242
5°	1447855
10°	1401772
15°	1194775
20°	852618
25°	523970
30°	282859
35°	136001
40°	65823
45°	35027
50°	20647
55°	13849
60°	8881
65°	6304
70°	5193
75°	3431
80°	5114
85°	0



TEST NUMBER: P219720

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	275.6	17.5
10°-20°	630.6	40.1
20°-30°	447.2	28.4
30°-40°	154.3	9.8
40°-50°	41.9	2.7
50°-60°	14.7	0.9
60°-70°	6.0	0.4
70°-80°	2.6	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1353.4	86.0
0°-40°	1507.7	95.8
0°-60°	1564.3	99.4
0°-90°	1573.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1573.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2879	
5°	2923	276
15°	2339	631
25°	962	447
35°	226	154
45°	50	42
55°	16	15
65°	5	6
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P219720

CATALOG NUMBER: MRZ-1-REC-X-4-L27-80-FL-UNV-X-STD

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2878.6
2.5°	2891.2
5°	2923.4
7.5°	2914.5
10°	2798.0
12.5°	2606.2
15°	2339.1
17.5°	1986.0
20°	1623.9
22.5°	1276.2
25°	962.5
27.5°	699.0
30°	496.5
32.5°	337.0
35°	225.8
37.5°	150.6
40°	102.2
42.5°	69.9
45°	50.2
47.5°	35.8
50°	26.9
52.5°	19.7
55°	16.1
57.5°	12.5
60°	9.0
62.5°	7.2
65°	5.4
67.5°	5.4
70°	3.6
72.5°	3.6
75°	1.8
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)