

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867277

Luminaire Tested: PRLX-2004-L-930-48L-L-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-85)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Pentalux
Catalog Number: PRLX-2004-L-930-48L-L-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
BELL WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2490.6 lumens
Efficiency: N/A
Efficacy: 66.4 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.99
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 37.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867277

CATALOG NUMBER: PRLX-2004-L-930-48L-L-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P867277

CATALOG NUMBER: PRLX-2004-L-930-48L-L-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99		100	98	97		96	95	94	92
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84	81	79	77
4	95	87	80	76	93	85	80	75	83	78	74		81	77	74		79	76	73	71
5	90	80	74	69	88	79	73	69	78	72	68		76	71	68		74	70	67	66
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	58		67	62	58		66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62	57	54	52
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	47		56	51	47		55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11475
5°	11085
10°	10544
15°	10135
20°	9765
25°	9421
30°	8966
35°	6504
40°	2311
45°	1017
50°	704
55°	694
60°	655
65°	616
70°	578
75°	547
80°	517
85°	481

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1017 cd/sqm

TEST NUMBER: P867277

CATALOG NUMBER: PRLX-2004-L-930-48L-L-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.4	8.4
10°-20°	558.8	22.4
20°-30°	795.5	31.9
30°-40°	630.7	25.3
40°-50°	132.2	5.3
50°-60°	71.6	2.9
60°-70°	52.5	2.1
70°-80°	30.4	1.2
80°-90°	9.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1563.7	62.8
0°-40°	2194.4	88.1
0°-60°	2398.2	96.3
0°-90°	2490.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2490.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2326	
5°	2238	209
15°	1984	559
25°	1731	795
35°	1080	631
45°	146	132
55°	81	72
65°	53	52
75°	29	30
85°	8	9
90°	0	

TEST NUMBER: P867277

CATALOG NUMBER: PRLX-2004-L-930-48L-L-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	2325.7
2.5°	2302.4
5°	2238.2
7.5°	2169.3
10°	2104.6
12.5°	2044.6
15°	1984.2
17.5°	1923.3
20°	1859.9
22.5°	1796.5
25°	1730.6
27.5°	1663.0
30°	1573.8
32.5°	1409.8
35°	1079.8
37.5°	663.5
40°	358.8
42.5°	219.3
45°	145.8
47.5°	106.1
50°	91.7
52.5°	87.1
55°	80.7
57.5°	73.5
60°	66.4
62.5°	59.6
65°	52.8
67.5°	46.5
70°	40.1
72.5°	34.2
75°	28.7
77.5°	23.2
80°	18.2
82.5°	13.1
85°	8.5
87.5°	4.2
90°	0.0

TEST NUMBER: P867277

CATALOG NUMBER: PRLX-2004-L-930-48L-L-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.55	6.61	5.92	6.92	7.23	5.55	6.61	5.92	6.92	7.23
	3H	7.18	8.11	7.56	8.45	8.82	7.18	8.11	7.56	8.45	8.82
	4H	7.81	8.67	8.21	9.03	9.41	7.81	8.67	8.21	9.03	9.41
	6H	8.28	9.08	8.70	9.45	9.85	8.28	9.08	8.70	9.45	9.85
	8H	8.45	9.19	8.88	9.59	9.99	8.45	9.19	8.88	9.59	9.99
	12H	8.55	9.27	8.99	9.65	10.08	8.55	9.27	8.99	9.65	10.08
4H	2H	6.04	6.91	6.45	7.26	7.65	6.04	6.91	6.45	7.26	7.65
	3H	7.88	8.59	8.29	9.00	9.40	7.88	8.59	8.29	9.00	9.40
	4H	8.63	9.27	9.07	9.69	10.14	8.63	9.27	9.07	9.69	10.14
	6H	9.24	9.79	9.71	10.24	10.71	9.24	9.79	9.71	10.24	10.71
	8H	9.45	9.96	9.92	10.41	10.88	9.45	9.96	9.92	10.41	10.88
	12H	9.60	10.04	10.09	10.53	11.01	9.60	10.04	10.09	10.53	11.01
8H	4H	8.86	9.37	9.34	9.82	10.30	8.86	9.37	9.34	9.82	10.30
	6H	9.62	10.02	10.12	10.52	11.01	9.62	10.02	10.12	10.52	11.01
	8H	9.91	10.27	10.44	10.79	11.29	9.91	10.27	10.44	10.79	11.29
	12H	10.16	10.47	10.68	10.97	11.55	10.16	10.47	10.68	10.97	11.55
12H	4H	8.87	9.31	9.36	9.80	10.27	8.87	9.31	9.36	9.80	10.27
	6H	9.66	10.02	10.19	10.54	11.03	9.66	10.02	10.19	10.54	11.03
	8H	10.01	10.32	10.53	10.82	11.40	10.01	10.32	10.53	10.82	11.40