

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219732

Luminaire Tested: **MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14876)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
40 DEGREE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 1
Light Source: (1) 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 274.4 lumens
Efficiency: N/A
Efficacy: 40.4 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 6.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219732

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P219732

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	88	84	80	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	75
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69
10	83	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	375166
5°	356442
10°	308260
15°	231232
20°	144124
25°	75724
30°	34125
35°	13190
40°	5152
45°	2582
50°	1228
55°	946
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219732

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.5	23.9
10°-20°	122.3	44.6
20°-30°	66.4	24.2
30°-40°	16.1	5.9
40°-50°	3.0	1.1
50°-60°	0.8	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.2	92.6
0°-40°	270.3	98.5
0°-60°	274.1	99.9
0°-90°	274.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	274.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	760	
5°	720	66
15°	453	122
25°	139	66
35°	22	16
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219732

CATALOG NUMBER: MRZ-1-REC-X-1H-L27-97-FL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

0°	
0°	760.4
2.5°	746.4
5°	719.7
7.5°	679.6
10°	615.3
12.5°	539.4
15°	452.7
17.5°	360.1
20°	274.5
22.5°	198.5
25°	139.1
27.5°	93.6
30°	59.9
32.5°	36.9
35°	21.9
37.5°	13.4
40°	8.0
42.5°	5.4
45°	3.7
47.5°	2.1
50°	1.6
52.5°	1.1
55°	1.1
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)