

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219647

Luminaire Tested: **MRZ-1-REC-X-2-L27-97-NFL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14873)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-2-L27-97-NFL-UNV-X-STD-SFL
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL2
Light Source: (1) 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 614.1 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.4
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219647

CATALOG NUMBER: MRZ-1-REC-X-2-L27-97-NFL-UNV-X-STD-SFL

Luminous Intensity Polar Plot





TEST NUMBER: P219647

CATALOG NUMBER: MRZ-1-REC-X-2-L27-97-NFL-UNV-X-STD-SFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	95	98	95	93	96	94	92	94	92	90	89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	85	90	87	85	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	78
8	92	85	80	77	91	84	80	77	83	80	77	82	79	77	82	79	76	75
9	89	82	78	75	88	82	78	75	81	77	75	80	77	74	79	76	74	73
10	87	80	76	73	86	79	75	73	79	75	73	78	75	72	77	74	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1376776
5°	1255940
10°	903537
15°	448826
20°	182873
25°	94396
30°	55432
35°	32163
40°	20288
45°	13815
50°	8980
55°	5677
60°	3651
65°	3386
70°	2164
75°	1334
80°	1989
85°	0



TEST NUMBER: P219647

CATALOG NUMBER: MRZ-1-REC-X-2-L27-97-NFL-UNV-X-STD-SFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.5	35.6
10°-20°	249.7	40.7
20°-30°	85.0	13.8
30°-40°	35.4	5.8
40°-50°	15.5	2.5
50°-60°	6.3	1.0
60°-70°	2.6	0.4
70°-80°	1.1	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.2	90.1
0°-40°	588.6	95.8
0°-60°	610.3	99.4
0°-90°	614.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2790	
5°	2536	219
15°	879	250
25°	173	85
35°	53	35
45°	20	15
55°	7	6
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P219647

CATALOG NUMBER: MRZ-1-REC-X-2-L27-97-NFL-UNV-X-STD-SFL

CANDELA DISTRIBUTION (FULL):

0°	
0°	2790.5
2.5°	2729.0
5°	2535.9
7.5°	2219.1
10°	1803.5
12.5°	1333.0
15°	878.7
17.5°	542.9
20°	348.3
22.5°	236.3
25°	173.4
27.5°	129.5
30°	97.3
32.5°	72.4
35°	53.4
37.5°	40.2
40°	31.5
42.5°	24.1
45°	19.8
47.5°	15.4
50°	11.7
52.5°	8.8
55°	6.6
57.5°	5.1
60°	3.7
62.5°	2.9
65°	2.9
67.5°	2.2
70°	1.5
72.5°	1.5
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)