

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867312

Luminaire Tested: PRLX-2004-L-935-117L-G-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867312
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-75)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-935-117L-G-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 7
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1553.4 lumens
Efficiency: N/A
Efficacy: 16.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.19
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 95.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867312

CATALOG NUMBER: PRLX-2004-L-935-117L-G-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P867312

CATALOG NUMBER: PRLX-2004-L-935-117L-G-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71	66	63	61
6	81	71	64	59	80	70	63	58	68	62	58		67	62	58		65	61	57	55
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61	56	52	51
8	72	60	53	49	70	60	53	48	59	53	48		58	52	48		56	51	48	46
9	67	56	49	45	66	56	49	44	55	49	44		54	48	44		53	48	44	42
10	64	52	45	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4672
5°	4690
10°	4713
15°	4720
20°	4731
25°	4769
30°	4648
35°	4149
40°	3438
45°	2577
50°	1597
55°	618
60°	133
65°	110
70°	89
75°	80
80°	88
85°	57

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2577 cd/sqm

TEST NUMBER: P867312

CATALOG NUMBER: PRLX-2004-L-935-117L-G-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.2	5.8
10°-20°	261.0	16.8
20°-30°	401.7	25.9
30°-40°	426.5	27.5
40°-50°	283.1	18.2
50°-60°	75.1	4.8
60°-70°	9.6	0.6
70°-80°	4.5	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	752.9	48.5
0°-40°	1179.5	75.9
0°-60°	1537.7	99.0
0°-90°	1553.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1553.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	947	
5°	947	90
15°	924	261
25°	876	402
35°	689	427
45°	369	283
55°	72	75
65°	9	10
75°	4	5
85°	1	2
90°	0	

TEST NUMBER: P867312

CATALOG NUMBER: PRLX-2004-L-935-117L-G-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	946.9
2.5°	946.9
5°	946.9
7.5°	945.9
10°	940.7
12.5°	933.4
15°	924.0
17.5°	912.6
20°	901.1
22.5°	888.6
25°	876.1
27.5°	857.4
30°	815.8
32.5°	759.6
35°	688.8
37.5°	615.0
40°	533.8
42.5°	452.6
45°	369.4
47.5°	287.2
50°	208.1
52.5°	136.3
55°	71.8
57.5°	23.9
60°	13.5
62.5°	11.4
65°	9.4
67.5°	8.3
70°	6.2
72.5°	5.2
75°	4.2
77.5°	3.1
80°	3.1
82.5°	2.1
85°	1.0
87.5°	1.0
90°	0.0

TEST NUMBER: P867312

CATALOG NUMBER: PRLX-2004-L-935-117L-G-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.22	0.00	0.53	0.85	0.00	0.22	0.00	0.53	0.85
	3H	0.00	0.54	0.00	0.87	1.24	0.00	0.54	0.00	0.87	1.24
	4H	0.00	0.62	0.05	0.97	1.36	0.00	0.62	0.05	0.97	1.36
	6H	0.00	0.66	0.19	1.03	1.43	0.00	0.66	0.19	1.03	1.43
	8H	0.00	0.67	0.26	1.06	1.47	0.00	0.67	0.26	1.06	1.47
	12H	0.00	0.64	0.27	1.02	1.45	0.00	0.64	0.27	1.02	1.45
4H	2H	0.00	0.03	0.00	0.38	0.76	0.00	0.03	0.00	0.38	0.76
	3H	0.00	0.45	0.08	0.86	1.26	0.00	0.45	0.08	0.86	1.26
	4H	0.00	0.60	0.34	1.02	1.46	0.00	0.60	0.34	1.02	1.46
	6H	0.14	0.73	0.60	1.18	1.65	0.14	0.73	0.60	1.18	1.65
	8H	0.23	0.79	0.71	1.24	1.71	0.23	0.79	0.71	1.24	1.71
	12H	0.27	0.76	0.76	1.24	1.72	0.27	0.76	0.76	1.24	1.72
8H	4H	0.00	0.47	0.38	0.92	1.39	0.00	0.47	0.38	0.92	1.39
	6H	0.25	0.70	0.75	1.20	1.69	0.25	0.70	0.75	1.20	1.69
	8H	0.40	0.81	0.93	1.33	1.83	0.40	0.81	0.93	1.33	1.83
	12H	0.49	0.85	1.01	1.35	1.92	0.49	0.85	1.01	1.35	1.92
12H	4H	0.00	0.38	0.38	0.86	1.34	0.00	0.38	0.38	0.86	1.34
	6H	0.25	0.66	0.77	1.17	1.67	0.25	0.66	0.77	1.17	1.67
	8H	0.44	0.81	0.96	1.30	1.88	0.44	0.81	0.96	1.30	1.88