

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P14876

Luminaire Tested: **MRZ-1-REC-X-3-L27-97-FL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P14876
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-3-L27-97-FL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
40 DEGREE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 3
Light Source: (1) 2700K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 513.0 lumens
Efficiency: N/A
Efficacy: 43.5 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P14876

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-FL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P14876

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-FL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	88	84	80	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	75
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69
10	83	76	71	68	83	75	71	68	75	71	68	74	70	68	73	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	701092
5°	666130
10°	576139
15°	432123
20°	269347
25°	141540
30°	63807
35°	24695
40°	9661
45°	4884
50°	2303
55°	1720
60°	987
65°	1167
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P14876

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-FL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	23.9
10°-20°	228.6	44.6
20°-30°	124.0	24.2
30°-40°	30.0	5.9
40°-50°	5.7	1.1
50°-60°	1.6	0.3
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	475.1	92.6
0°-40°	505.2	98.5
0°-60°	512.4	99.9
0°-90°	513.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	513.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1421	
5°	1345	122
15°	846	229
25°	260	124
35°	41	30
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P14876

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-FL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

	0°
0°	1421
2.5°	1395
5°	1345
7.5°	1270
10°	1150
12.5°	1008
15°	846
17.5°	673
20°	513
22.5°	371
25°	260
27.5°	175
30°	112
32.5°	69
35°	41
37.5°	25
40°	15
42.5°	10
45°	7
47.5°	4
50°	3
52.5°	2
55°	2
57.5°	1
60°	1
62.5°	1
65°	1
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)