

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P14881

Luminaire Tested: **MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P14881  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD-HEX  
Description: MRZ INTEGRAL LED DOWNLIGHT  
55 DEGREE WIDE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 3  
Light Source: (1) 2700K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 379.2 lumens  
Efficiency: N/A  
Efficacy: 31.9 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.67  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P14881

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD-HEX

### Luminous Intensity Polar Plot





TEST NUMBER: P14881

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD-HEX

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	81	78	84	80	78	83	79	77	76
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	60	68	63	60	67	63	60	67	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	366581
5°	346685
10°	306606
15°	248241
20°	189016
25°	139907
30°	90013
35°	47582
40°	20610
45°	7675
50°	3070
55°	1720
60°	987
65°	1167
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P14881

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD-HEX

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.1	16.9
10°-20°	133.8	35.3
20°-30°	116.7	30.8
30°-40°	51.7	13.6
40°-50°	10.2	2.7
50°-60°	2.1	0.6
60°-70°	0.6	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.6	83.0
0°-40°	366.3	96.6
0°-60°	378.6	99.8
0°-90°	379.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	379.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	743	
5°	700	64
15°	486	134
25°	257	117
35°	79	52
45°	11	10
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P14881

CATALOG NUMBER: MRZ-1-REC-X-3-L27-97-WFL-UNV-X-STD-HEX

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	743
2.5°	728
5°	700
7.5°	662
10°	612
12.5°	551
15°	486
17.5°	418
20°	360
22.5°	309
25°	257
27.5°	207
30°	158
32.5°	114
35°	79
37.5°	51
40°	32
42.5°	18
45°	11
47.5°	7
50°	4
52.5°	3
55°	2
57.5°	2
60°	1
62.5°	1
65°	1
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)