

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867321

Luminaire Tested: PRLX-2004-L-935-133L-G-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P867321  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-L-935-133L-G-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,  
BELL WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 8  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2681.1 lumens  
Efficiency: N/A  
Efficacy: 24.0 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.17  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 111.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P867321

CATALOG NUMBER: PRLX-2004-L-935-133L-G-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P867321

CATALOG NUMBER: PRLX-2004-L-935-133L-G-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71
4	91	81	74	69	89	80	73	68	78	72	67	75	70	67	73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	60	69	64	60	68	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	49	45	43
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	7790
5°	7801
10°	7778
15°	7699
20°	7582
25°	7421
30°	7080
35°	6366
40°	5441
45°	4348
50°	3155
55°	1937
60°	1093
65°	932
70°	825
75°	749
80°	676
85°	606

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4348 cd/sqm

TEST NUMBER: P867321

CATALOG NUMBER: PRLX-2004-L-935-133L-G-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.6	5.6
10°-20°	424.8	15.8
20°-30°	625.3	23.3
30°-40°	656.4	24.5
40°-50°	479.2	17.9
50°-60°	211.1	7.9
60°-70°	80.5	3.0
70°-80°	41.8	1.6
80°-90°	12.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1199.8	44.7
0°-40°	1856.2	69.2
0°-60°	2546.5	95.0
0°-90°	2681.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2681.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1579	
5°	1575	150
15°	1507	425
25°	1363	625
35°	1057	656
45°	623	479
55°	225	211
65°	80	81
75°	39	42
85°	11	12
90°	0	

TEST NUMBER: P867321

CATALOG NUMBER: PRLX-2004-L-935-133L-G-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1578.8
2.5°	1577.6
5°	1575.2
7.5°	1566.8
10°	1552.6
12.5°	1532.3
15°	1507.3
17.5°	1478.7
20°	1444.1
22.5°	1407.2
25°	1363.1
27.5°	1313.1
30°	1242.8
32.5°	1157.0
35°	1056.9
37.5°	953.2
40°	844.8
42.5°	734.0
45°	623.2
47.5°	513.5
50°	411.1
52.5°	314.6
55°	225.2
57.5°	152.5
60°	110.8
62.5°	94.1
65°	79.8
67.5°	67.9
70°	57.2
72.5°	47.7
75°	39.3
77.5°	31.0
80°	23.8
82.5°	17.9
85°	10.7
87.5°	4.8
90°	0.0



TEST NUMBER: P867321  
 CATALOG NUMBER: PRLX-2004-L-935-133L-G-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.96	11.27	10.33	11.58	11.89	9.96	11.27	10.33	11.58	11.89
	3H	10.85	12.00	11.23	12.33	12.69	10.85	12.00	11.23	12.33	12.69
	4H	11.20	12.27	11.60	12.62	13.00	11.20	12.27	11.60	12.62	13.00
	6H	11.46	12.44	11.88	12.81	13.21	11.46	12.44	11.88	12.81	13.21
	8H	11.55	12.48	11.98	12.87	13.28	11.55	12.48	11.98	12.87	13.28
	12H	11.61	12.50	12.04	12.88	13.31	11.61	12.50	12.04	12.88	13.31
4H	2H	10.19	11.26	10.59	11.61	11.99	10.19	11.26	10.59	11.61	11.99
	3H	11.29	12.16	11.70	12.56	12.97	11.29	12.16	11.70	12.56	12.97
	4H	11.76	12.54	12.20	12.96	13.40	11.76	12.54	12.20	12.96	13.40
	6H	12.14	12.81	12.61	13.26	13.73	12.14	12.81	12.61	13.26	13.73
	8H	12.28	12.91	12.75	13.35	13.83	12.28	12.91	12.75	13.35	13.83
	12H	12.38	12.93	12.86	13.41	13.89	12.38	12.93	12.86	13.41	13.89
8H	4H	11.89	12.52	12.36	12.97	13.44	11.89	12.52	12.36	12.97	13.44
	6H	12.38	12.89	12.88	13.39	13.87	12.38	12.89	12.88	13.39	13.87
	8H	12.59	13.05	13.11	13.56	14.06	12.59	13.05	13.11	13.56	14.06
	12H	12.75	13.16	13.27	13.66	14.23	12.75	13.16	13.27	13.66	14.23
12H	4H	11.89	12.44	12.37	12.92	13.40	11.89	12.44	12.37	12.92	13.40
	6H	12.40	12.86	12.92	13.37	13.87	12.40	12.86	12.92	13.37	13.87
	8H	12.65	13.06	13.17	13.56	14.13	12.65	13.06	13.17	13.56	14.13