

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867316

Luminaire Tested: PRLX-2004-L-935-133L-L-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P867316  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-87)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-L-935-133L-L-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,  
BELL WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 8  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5885.1 lumens  
Efficiency: N/A  
Efficacy: 52.6 lumens/watt  
Spacing Criteria (0/90/45): 1.05 / 1.05 / 0.98  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 111.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P867316

CATALOG NUMBER: PRLX-2004-L-935-133L-L-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P867316

CATALOG NUMBER: PRLX-2004-L-935-133L-L-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65
7	83	74	68	63	82	73	67	63	72	66	63	70	66	62	69	65	62	61
8	79	69	63	59	78	69	63	59	68	62	59	66	62	58	65	61	58	57
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	54	53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	29893
5°	29099
10°	27746
15°	26681
20°	25731
25°	24830
30°	23765
35°	16033
40°	3868
45°	989
50°	348
55°	328
60°	306
65°	278
70°	258
75°	250
80°	236
85°	204

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 989 cd/sqm

TEST NUMBER: P867316

CATALOG NUMBER: PRLX-2004-L-935-133L-L-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	549.9	9.3
10°-20°	1471.2	25.0
20°-30°	2097.6	35.6
30°-40°	1535.0	26.1
40°-50°	155.4	2.6
50°-60°	34.1	0.6
60°-70°	23.7	0.4
70°-80°	13.8	0.2
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4118.7	70.0
0°-40°	5653.7	96.1
0°-60°	5843.2	99.3
0°-90°	5885.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5885.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6059	
5°	5875	550
15°	5224	1471
25°	4561	2098
35°	2662	1535
45°	142	155
55°	38	34
65°	24	24
75°	13	14
85°	4	4
90°	0	

TEST NUMBER: P867316

CATALOG NUMBER: PRLX-2004-L-935-133L-L-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	6058.9
2.5°	6017.2
5°	5875.4
7.5°	5703.8
10°	5538.2
12.5°	5380.9
15°	5223.6
17.5°	5065.2
20°	4900.7
22.5°	4730.3
25°	4561.1
27.5°	4383.6
30°	4171.5
32.5°	3684.2
35°	2661.9
37.5°	1353.6
40°	600.5
42.5°	318.1
45°	141.8
47.5°	50.0
50°	45.3
52.5°	41.7
55°	38.1
57.5°	34.6
60°	31.0
62.5°	27.4
65°	23.8
67.5°	20.3
70°	17.9
72.5°	15.5
75°	13.1
77.5°	10.7
80°	8.3
82.5°	6.0
85°	3.6
87.5°	2.4
90°	0.0



TEST NUMBER: P867316

CATALOG NUMBER: PRLX-2004-L-935-133L-L-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.06	0.43	0.00	0.00	0.00	0.06	0.43
	4H	0.00	0.28	0.00	0.63	1.02	0.00	0.28	0.00	0.63	1.02
	6H	0.00	0.68	0.41	1.06	1.46	0.00	0.68	0.41	1.06	1.46
	8H	0.15	0.80	0.59	1.19	1.60	0.15	0.80	0.59	1.19	1.60
	12H	0.24	0.85	0.67	1.24	1.67	0.24	0.85	0.67	1.24	1.67
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.17	0.00	0.58	0.99	0.00	0.17	0.00	0.58	0.99
	4H	0.29	0.84	0.73	1.27	1.72	0.29	0.84	0.73	1.27	1.72
	6H	0.90	1.37	1.37	1.82	2.29	0.90	1.37	1.37	1.82	2.29
	8H	1.10	1.54	1.58	1.99	2.46	1.10	1.54	1.58	1.99	2.46
	12H	1.23	1.60	1.72	2.09	2.57	1.23	1.60	1.72	2.09	2.57
8H	4H	0.51	0.94	0.99	1.39	1.87	0.51	0.94	0.99	1.39	1.87
	6H	1.26	1.60	1.77	2.10	2.59	1.26	1.60	1.77	2.10	2.59
	8H	1.55	1.85	2.08	2.37	2.87	1.55	1.85	2.08	2.37	2.87
	12H	1.77	2.03	2.29	2.52	3.11	1.77	2.03	2.29	2.52	3.11
12H	4H	0.50	0.88	1.00	1.37	1.85	0.50	0.88	1.00	1.37	1.85
	6H	1.29	1.60	1.83	2.12	2.62	1.29	1.60	1.83	2.12	2.62
	8H	1.64	1.90	2.16	2.40	2.98	1.64	1.90	2.16	2.40	2.98