

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867317

Luminaire Tested: PRLX-2004-L-935-133L-L-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867317
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-85)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-935-133L-L-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
BELL WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7022.0 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.99
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 111.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867317

CATALOG NUMBER: PRLX-2004-L-935-133L-L-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P867317

CATALOG NUMBER: PRLX-2004-L-935-133L-L-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77
4	95	87	80	76	93	85	80	75	83	78	74	81	77	74	79	76	73	71
5	90	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	66
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	58	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32351
5°	31253
10°	29728
15°	28574
20°	27533
25°	26562
30°	25279
35°	18336
40°	6515
45°	2868
50°	1985
55°	1958
60°	1846
65°	1738
70°	1633
75°	1544
80°	1455
85°	1347

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2868 cd/sqm

TEST NUMBER: P867317

CATALOG NUMBER: PRLX-2004-L-935-133L-L-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	590.5	8.4
10°-20°	1575.4	22.4
20°-30°	2242.8	31.9
30°-40°	1778.3	25.3
40°-50°	372.7	5.3
50°-60°	202.0	2.9
60°-70°	148.0	2.1
70°-80°	85.8	1.2
80°-90°	26.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4408.6	62.8
0°-40°	6186.9	88.1
0°-60°	6761.6	96.3
0°-90°	7022.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7022.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6557	
5°	6310	590
15°	5594	1575
25°	4879	2243
35°	3044	1778
45°	411	373
55°	228	202
65°	149	148
75°	81	86
85°	24	27
90°	0	

TEST NUMBER: P867317

CATALOG NUMBER: PRLX-2004-L-935-133L-L-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	6556.9
2.5°	6491.4
5°	6310.3
7.5°	6116.1
10°	5933.8
12.5°	5764.6
15°	5594.2
17.5°	5422.6
20°	5243.9
22.5°	5065.2
25°	4879.3
27.5°	4688.6
30°	4437.2
32.5°	3974.9
35°	3044.3
37.5°	1870.7
40°	1011.6
42.5°	618.4
45°	411.1
47.5°	299.1
50°	258.6
52.5°	245.5
55°	227.6
57.5°	207.3
60°	187.1
62.5°	168.0
65°	148.9
67.5°	131.1
70°	113.2
72.5°	96.5
75°	81.0
77.5°	65.5
80°	51.2
82.5°	36.9
85°	23.8
87.5°	11.9
90°	0.0



TEST NUMBER: P867317

CATALOG NUMBER: PRLX-2004-L-935-133L-L-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.15	10.21	9.52	10.52	10.84	9.15	10.21	9.52	10.52	10.84
	3H	10.78	11.72	11.17	12.05	12.42	10.78	11.72	11.17	12.05	12.42
	4H	11.41	12.28	11.82	12.63	13.02	11.41	12.28	11.82	12.63	13.02
	6H	11.89	12.68	12.31	13.06	13.45	11.89	12.68	12.31	13.06	13.45
	8H	12.05	12.80	12.48	13.19	13.60	12.05	12.80	12.48	13.19	13.60
	12H	12.16	12.87	12.59	13.25	13.68	12.16	12.87	12.59	13.25	13.68
4H	2H	9.64	10.51	10.05	10.86	11.25	9.64	10.51	10.05	10.86	11.25
	3H	11.48	12.19	11.90	12.60	13.01	11.48	12.19	11.90	12.60	13.01
	4H	12.24	12.87	12.67	13.29	13.74	12.24	12.87	12.67	13.29	13.74
	6H	12.85	13.39	13.31	13.84	14.31	12.85	13.39	13.31	13.84	14.31
	8H	13.05	13.56	13.53	14.01	14.48	13.05	13.56	13.53	14.01	14.48
	12H	13.20	13.64	13.69	14.13	14.61	13.20	13.64	13.69	14.13	14.61
8H	4H	12.47	12.98	12.94	13.43	13.90	12.47	12.98	12.94	13.43	13.90
	6H	13.22	13.62	13.73	14.13	14.61	13.22	13.62	13.73	14.13	14.61
	8H	13.51	13.87	14.04	14.39	14.89	13.51	13.87	14.04	14.39	14.89
	12H	13.76	14.07	14.28	14.57	15.15	13.76	14.07	14.28	14.57	15.15
12H	4H	12.47	12.91	12.96	13.40	13.88	12.47	12.91	12.96	13.40	13.88
	6H	13.26	13.62	13.79	14.14	14.64	13.26	13.62	13.79	14.14	14.64
	8H	13.62	13.93	14.14	14.42	15.00	13.62	13.93	14.14	14.42	15.00