

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867376

Luminaire Tested: PRLX-2004-L-940-117L-G-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867376
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-75)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-940-117L-G-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 7
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1621.8 lumens
Efficiency: N/A
Efficacy: 17.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.19
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 95.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867376

CATALOG NUMBER: PRLX-2004-L-940-117L-G-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P867376

CATALOG NUMBER: PRLX-2004-L-940-117L-G-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	51
8	72	60	53	49	70	60	53	48	59	53	48	58	52	48	56	51	48	46
9	67	56	49	45	66	56	49	44	55	49	44	54	48	44	53	48	44	42
10	64	52	45	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4877
5°	4896
10°	4920
15°	4927
20°	4939
25°	4979
30°	4852
35°	4331
40°	3589
45°	2691
50°	1668
55°	645
60°	139
65°	114
70°	94
75°	82
80°	94
85°	62

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2691 cd/sqm

TEST NUMBER: P867376

CATALOG NUMBER: PRLX-2004-L-940-117L-G-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	5.8
10°-20°	272.4	16.8
20°-30°	419.4	25.9
30°-40°	445.3	27.5
40°-50°	295.6	18.2
50°-60°	78.4	4.8
60°-70°	10.1	0.6
70°-80°	4.7	0.3
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	786.0	48.5
0°-40°	1231.3	75.9
0°-60°	1605.3	99.0
0°-90°	1621.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1621.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	988	
5°	988	94
15°	965	272
25°	915	419
35°	719	445
45°	386	296
55°	75	78
65°	10	10
75°	4	5
85°	1	2
90°	0	

TEST NUMBER: P867376

CATALOG NUMBER: PRLX-2004-L-940-117L-G-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	988.5
2.5°	988.5
5°	988.5
7.5°	987.5
10°	982.0
12.5°	974.4
15°	964.6
17.5°	952.7
20°	940.7
22.5°	927.7
25°	914.7
27.5°	895.1
30°	851.7
32.5°	793.0
35°	719.1
37.5°	642.0
40°	557.3
42.5°	472.5
45°	385.6
47.5°	299.8
50°	217.3
52.5°	142.3
55°	75.0
57.5°	25.0
60°	14.1
62.5°	11.9
65°	9.8
67.5°	8.7
70°	6.5
72.5°	5.4
75°	4.3
77.5°	3.3
80°	3.3
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

TEST NUMBER: P867376

CATALOG NUMBER: PRLX-2004-L-940-117L-G-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.39	0.00	0.70	1.01	0.00	0.39	0.00	0.70	1.01
	3H	0.00	0.71	0.04	1.04	1.40	0.00	0.71	0.04	1.04	1.40
	4H	0.00	0.78	0.21	1.13	1.52	0.00	0.78	0.21	1.13	1.52
	6H	0.00	0.83	0.35	1.20	1.59	0.00	0.83	0.35	1.20	1.59
	8H	0.00	0.84	0.43	1.23	1.63	0.00	0.84	0.43	1.23	1.63
	12H	0.01	0.81	0.44	1.19	1.62	0.01	0.81	0.44	1.19	1.62
4H	2H	0.00	0.19	0.00	0.54	0.93	0.00	0.19	0.00	0.54	0.93
	3H	0.00	0.61	0.24	1.02	1.42	0.00	0.61	0.24	1.02	1.42
	4H	0.05	0.75	0.49	1.17	1.62	0.05	0.75	0.49	1.17	1.62
	6H	0.30	0.90	0.77	1.35	1.82	0.30	0.90	0.77	1.35	1.82
	8H	0.40	0.96	0.87	1.41	1.88	0.40	0.96	0.87	1.41	1.88
	12H	0.44	0.93	0.93	1.41	1.89	0.44	0.93	0.93	1.41	1.89
8H	4H	0.06	0.62	0.54	1.07	1.54	0.06	0.62	0.54	1.07	1.54
	6H	0.42	0.87	0.92	1.37	1.85	0.42	0.87	0.92	1.37	1.85
	8H	0.58	0.99	1.10	1.50	2.00	0.58	0.99	1.10	1.50	2.00
	12H	0.67	1.03	1.18	1.53	2.10	0.67	1.03	1.18	1.53	2.10
12H	4H	0.04	0.53	0.53	1.02	1.49	0.04	0.53	0.53	1.02	1.49
	6H	0.42	0.82	0.94	1.34	1.84	0.42	0.82	0.94	1.34	1.84
	8H	0.62	0.98	1.14	1.48	2.05	0.62	0.98	1.14	1.48	2.05