

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P226125

Luminaire Tested: **MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P226125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14880)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD
Description: MRZ INTEGRAL LED DOWNLIGHT
55 DEGREE WIDE FLOOD OPTIC, LIGHT LEVEL 1
Light Source: (1) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 555.8 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.91
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 5.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P226125

CATALOG NUMBER: MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD

Luminous Intensity Polar Plot





TEST NUMBER: P226125

CATALOG NUMBER: MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85	82	80	78
4	95	87	81	77	94	86	81	76	84	79	76		82	78	75		80	77	74	72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75	71	68	67
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71	66	63	62
7	81	71	64	60	79	70	64	60	69	63	59		68	63	59		66	62	59	57
8	76	66	60	56	75	66	60	56	65	59	55		64	59	55		63	58	55	53
9	73	62	56	52	71	62	56	52	61	55	52		60	55	51		59	55	51	50
10	69	59	53	49	68	58	52	48	57	52	48		57	52	48		56	51	48	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	275207
5°	276655
10°	268932
15°	246045
20°	220046
25°	197775
30°	162765
35°	116004
40°	76708
45°	48912
50°	30319
55°	18752
60°	10756
65°	5487
70°	3029
75°	2478
80°	0
85°	0



TEST NUMBER: P226125

CATALOG NUMBER: MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	9.5
10°-20°	134.3	24.2
20°-30°	164.5	29.6
30°-40°	121.4	21.8
40°-50°	56.1	10.1
50°-60°	20.4	3.7
60°-70°	5.3	0.9
70°-80°	1.1	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	351.5	63.2
0°-40°	472.9	85.1
0°-60°	549.4	98.8
0°-90°	555.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	555.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	558	
5°	559	53
15°	482	134
25°	363	165
35°	193	121
45°	70	56
55°	22	20
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P226125

CATALOG NUMBER: MRZ-1-REC-X-1-L30-80-WFL-UNV-X-STD

CANDELA DISTRIBUTION (FULL):

0°	
0°	557.8
2.5°	557.2
5°	558.6
7.5°	552.4
10°	536.8
12.5°	512.9
15°	481.7
17.5°	447.7
20°	419.1
22.5°	393.9
25°	363.3
27.5°	327.9
30°	285.7
32.5°	238.8
35°	192.6
37.5°	152.4
40°	119.1
42.5°	91.9
45°	70.1
47.5°	53.0
50°	39.5
52.5°	29.3
55°	21.8
57.5°	15.6
60°	10.9
62.5°	7.5
65°	4.7
67.5°	2.7
70°	2.1
72.5°	1.3
75°	1.3
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)