

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219799

Luminaire Tested: **MRZ-1-REC-X-2-L30-80-FL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219799
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14878)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-2-L30-80-FL-UNV-X-STD-SFL
Description: MRZ INTEGRAL LED DOWNLIGHT
40 DEGREE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL2
Light Source: (1) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 866.7 lumens
Efficiency: N/A
Efficacy: 98.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219799

CATALOG NUMBER: MRZ-1-REC-X-2-L30-80-FL-UNV-X-STD-SFL

Luminous Intensity Polar Plot





TEST NUMBER: P219799

CATALOG NUMBER: MRZ-1-REC-X-2-L30-80-FL-UNV-X-STD-SFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94
2	109	105	101	98	107	103	99	97	100	97	95	97	94	93	94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	88	85	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75
6	91	83	78	74	90	83	78	74	81	77	73	80	76	73	79	75	73	71
7	88	79	74	70	86	79	74	70	77	73	70	76	72	69	75	72	69	68
8	84	76	70	67	83	75	70	66	74	69	66	73	69	66	72	68	66	64
9	81	72	67	63	80	72	67	63	71	66	63	70	66	63	69	65	63	61
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	762962
5°	763301
10°	727238
15°	615291
20°	450855
25°	289286
30°	165044
35°	87876
40°	46952
45°	26933
50°	16810
55°	11612
60°	8190
65°	6071
70°	4472
75°	4003
80°	2841
85°	0



TEST NUMBER: P219799

CATALOG NUMBER: MRZ-1-REC-X-2-L30-80-FL-UNV-X-STD-SFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.4	16.7
10°-20°	327.5	37.8
20°-30°	245.7	28.4
30°-40°	97.5	11.3
40°-50°	31.8	3.7
50°-60°	12.4	1.4
60°-70°	5.3	0.6
70°-80°	1.9	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	717.6	82.8
0°-40°	815.1	94.1
0°-60°	859.4	99.2
0°-90°	866.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	866.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1546	
5°	1541	144
15°	1205	327
25°	531	246
35°	146	98
45°	39	32
55°	14	12
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P219799

CATALOG NUMBER: MRZ-1-REC-X-2-L30-80-FL-UNV-X-STD-SFL

CANDELA DISTRIBUTION (FULL):

0°	
0°	1546.4
2.5°	1548.5
5°	1541.2
7.5°	1515.1
10°	1451.6
12.5°	1347.4
15°	1204.6
17.5°	1036.8
20°	858.7
22.5°	686.7
25°	531.4
27.5°	398.1
30°	289.7
32.5°	207.4
35°	145.9
37.5°	103.2
40°	72.9
42.5°	53.1
45°	38.6
47.5°	28.1
50°	21.9
52.5°	16.7
55°	13.5
57.5°	10.4
60°	8.3
62.5°	6.3
65°	5.2
67.5°	4.2
70°	3.1
72.5°	2.1
75°	2.1
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)