

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219745

Luminaire Tested: **MRZ-1-REC-X-3-L30-80-FL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219745
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14876)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-3-L30-80-FL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
40 DEGREE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 3
Light Source: (1) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 730.6 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219745

CATALOG NUMBER: MRZ-1-REC-X-3-L30-80-FL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P219745

CATALOG NUMBER: MRZ-1-REC-X-3-L30-80-FL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	88	84	80	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	75
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69
10	83	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	998551
5°	948728
10°	820573
15°	615444
20°	383597
25°	201585
30°	90868
35°	35175
40°	13783
45°	6977
50°	3301
55°	2409
60°	1381
65°	1634
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219745

CATALOG NUMBER: MRZ-1-REC-X-3-L30-80-FL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.4	23.9
10°-20°	325.6	44.6
20°-30°	176.7	24.2
30°-40°	42.8	5.9
40°-50°	8.1	1.1
50°-60°	2.2	0.3
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	676.7	92.6
0°-40°	719.5	98.5
0°-60°	729.7	99.9
0°-90°	730.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	730.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2024	
5°	1916	174
15°	1205	326
25°	370	177
35°	58	43
45°	10	8
55°	3	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219745

CATALOG NUMBER: MRZ-1-REC-X-3-L30-80-FL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

0°	
0°	2023.9
2.5°	1986.8
5°	1915.6
7.5°	1808.8
10°	1637.9
12.5°	1435.7
15°	1204.9
17.5°	958.5
20°	730.6
22.5°	528.4
25°	370.3
27.5°	249.2
30°	159.5
32.5°	98.3
35°	58.4
37.5°	35.6
40°	21.4
42.5°	14.2
45°	10.0
47.5°	5.7
50°	4.3
52.5°	2.8
55°	2.8
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)