

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867424

Luminaire Tested: PRLX-2004-L-940-83L-G-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867424
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-75)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-940-83L-G-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1151.1 lumens
Efficiency: N/A
Efficacy: 17.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.19
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 64.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867424

CATALOG NUMBER: PRLX-2004-L-940-83L-G-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P867424

CATALOG NUMBER: PRLX-2004-L-940-83L-G-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	76	72	80	75	71		78	74	70		76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71	66	63	61
6	81	71	64	59	80	70	63	58	68	62	58		67	62	58		65	61	57	55
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61	56	52	51
8	72	60	53	49	70	60	53	48	59	53	48		58	52	48		56	51	48	46
9	67	56	49	45	66	56	49	44	55	49	44		54	48	44		53	48	44	42
10	64	52	45	41	62	52	45	41	51	45	41		50	45	41		49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3462
5°	3475
10°	3492
15°	3497
20°	3506
25°	3535
30°	3444
35°	3075
40°	2548
45°	1910
50°	1184
55°	458
60°	99
65°	81
70°	66
75°	59
80°	65
85°	45

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1910 cd/sqm

TEST NUMBER: P867424

CATALOG NUMBER: PRLX-2004-L-940-83L-G-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.9	5.8
10°-20°	193.4	16.8
20°-30°	297.7	25.9
30°-40°	316.1	27.5
40°-50°	209.8	18.2
50°-60°	55.7	4.8
60°-70°	7.1	0.6
70°-80°	3.4	0.3
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.0	48.5
0°-40°	874.1	75.9
0°-60°	1139.5	99.0
0°-90°	1151.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1151.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	702	
5°	702	67
15°	685	193
25°	649	298
35°	510	316
45°	274	210
55°	53	56
65°	7	7
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P867424

CATALOG NUMBER: PRLX-2004-L-940-83L-G-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	701.7
2.5°	701.7
5°	701.7
7.5°	700.9
10°	697.1
12.5°	691.7
15°	684.7
17.5°	676.2
20°	667.8
22.5°	658.5
25°	649.3
27.5°	635.4
30°	604.5
32.5°	562.9
35°	510.5
37.5°	455.7
40°	395.6
42.5°	335.4
45°	273.7
47.5°	212.8
50°	154.2
52.5°	101.0
55°	53.2
57.5°	17.7
60°	10.0
62.5°	8.5
65°	6.9
67.5°	6.2
70°	4.6
72.5°	3.9
75°	3.1
77.5°	2.3
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0



TEST NUMBER: P867424
 CATALOG NUMBER: PRLX-2004-L-940-83L-G-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.20	0.00	0.00	0.00	0.00	0.20
	4H	0.00	0.00	0.00	0.00	0.32	0.00	0.00	0.00	0.00	0.32
	6H	0.00	0.00	0.00	0.00	0.39	0.00	0.00	0.00	0.00	0.39
	8H	0.00	0.00	0.00	0.02	0.43	0.00	0.00	0.00	0.02	0.43
	12H	0.00	0.00	0.00	0.00	0.41	0.00	0.00	0.00	0.00	0.41
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.22	0.00	0.00	0.00	0.00	0.22
	4H	0.00	0.00	0.00	0.00	0.42	0.00	0.00	0.00	0.00	0.42
	6H	0.00	0.00	0.00	0.14	0.61	0.00	0.00	0.00	0.14	0.61
	8H	0.00	0.00	0.00	0.19	0.67	0.00	0.00	0.00	0.19	0.67
	12H	0.00	0.00	0.00	0.20	0.68	0.00	0.00	0.00	0.20	0.68
8H	4H	0.00	0.00	0.00	0.00	0.35	0.00	0.00	0.00	0.00	0.35
	6H	0.00	0.00	0.00	0.16	0.64	0.00	0.00	0.00	0.16	0.64
	8H	0.00	0.00	0.00	0.28	0.78	0.00	0.00	0.00	0.28	0.78
	12H	0.00	0.00	0.00	0.30	0.88	0.00	0.00	0.00	0.30	0.88
12H	4H	0.00	0.00	0.00	0.00	0.30	0.00	0.00	0.00	0.00	0.30
	6H	0.00	0.00	0.00	0.13	0.63	0.00	0.00	0.00	0.13	0.63
	8H	0.00	0.00	0.00	0.25	0.83	0.00	0.00	0.00	0.25	0.83