

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867422

Luminaire Tested: PRLX-2004-L-940-83L-L-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P867422  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-86)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-L-940-83L-L-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,  
BELL WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 5  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4529.2 lumens  
Efficiency: N/A  
Efficacy: 70.2 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.98  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 64.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P867422

CATALOG NUMBER: PRLX-2004-L-940-83L-L-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P867422

CATALOG NUMBER: PRLX-2004-L-940-83L-L-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	77
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53
9	72	62	56	51	71	62	55	51	61	55	51	60	55	51	59	54	51	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	21430
5°	20733
10°	19648
15°	18795
20°	18048
25°	17345
30°	16561
35°	11602
40°	3651
45°	1770
50°	1320
55°	1273
60°	1187
65°	1099
70°	1023
75°	955
80°	898
85°	832

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1770 cd/sqm

TEST NUMBER: P867422

CATALOG NUMBER: PRLX-2004-L-940-83L-L-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	391.0	8.6
10°-20°	1036.5	22.9
20°-30°	1465.9	32.4
30°-40°	1116.3	24.6
40°-50°	224.4	5.0
50°-60°	131.6	2.9
60°-70°	93.6	2.1
70°-80°	53.4	1.2
80°-90°	16.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2893.4	63.9
0°-40°	4009.7	88.5
0°-60°	4365.7	96.4
0°-90°	4529.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4529.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4344	
5°	4186	391
15°	3680	1036
25°	3186	1466
35°	1926	1116
45°	254	224
55°	148	132
65°	94	94
75°	50	53
85°	15	16
90°	0	

TEST NUMBER: P867422

CATALOG NUMBER: PRLX-2004-L-940-83L-L-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4343.5
2.5°	4311.2
5°	4186.2
7.5°	4045.9
10°	3921.8
12.5°	3802.2
15°	3679.6
17.5°	3562.4
20°	3437.5
22.5°	3311.1
25°	3186.1
27.5°	3059.7
30°	2907.0
32.5°	2583.9
35°	1926.2
37.5°	1064.9
40°	566.8
42.5°	374.7
45°	253.7
47.5°	182.7
50°	172.0
52.5°	161.2
55°	148.0
57.5°	133.4
60°	120.3
62.5°	106.4
65°	94.1
67.5°	82.5
70°	70.9
72.5°	60.1
75°	50.1
77.5°	40.9
80°	31.6
82.5°	23.1
85°	14.7
87.5°	6.9
90°	0.0

TEST NUMBER: P867422  
 CATALOG NUMBER: PRLX-2004-L-940-83L-L-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.62	8.67	7.99	8.98	9.30	7.62	8.67	7.99	8.98	9.30
	3H	9.18	10.11	9.57	10.44	10.81	9.18	10.11	9.57	10.44	10.81
	4H	9.77	10.64	10.18	10.99	11.38	9.77	10.64	10.18	10.99	11.38
	6H	10.23	11.02	10.65	11.39	11.79	10.23	11.02	10.65	11.39	11.79
	8H	10.39	11.13	10.82	11.52	11.93	10.39	11.13	10.82	11.52	11.93
	12H	10.49	11.20	10.92	11.58	12.01	10.49	11.20	10.92	11.58	12.01
4H	2H	8.08	8.95	8.49	9.30	9.69	8.08	8.95	8.49	9.30	9.69
	3H	9.86	10.56	10.27	10.97	11.38	9.86	10.56	10.27	10.97	11.38
	4H	10.57	11.20	11.01	11.63	12.07	10.57	11.20	11.01	11.63	12.07
	6H	11.16	11.70	11.63	12.15	12.62	11.16	11.70	11.63	12.15	12.62
	8H	11.36	11.87	11.84	12.32	12.79	11.36	11.87	11.84	12.32	12.79
	12H	11.51	11.94	12.00	12.43	12.91	11.51	11.94	12.00	12.43	12.91
8H	4H	10.79	11.30	11.27	11.75	12.22	10.79	11.30	11.27	11.75	12.22
	6H	11.52	11.92	12.03	12.42	12.91	11.52	11.92	12.03	12.42	12.91
	8H	11.81	12.16	12.34	12.69	13.18	11.81	12.16	12.34	12.69	13.18
	12H	12.05	12.35	12.57	12.85	13.43	12.05	12.35	12.57	12.85	13.43
12H	4H	10.79	11.23	11.28	11.72	12.20	10.79	11.23	11.28	11.72	12.20
	6H	11.56	11.91	12.09	12.44	12.93	11.56	11.91	12.09	12.44	12.93
	8H	11.91	12.21	12.43	12.71	13.29	11.91	12.21	12.43	12.71	13.29