

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219931

Luminaire Tested: **MRZ-1-REC-X-3-L30-80-WFL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219931  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14883)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-3-L30-80-WFL-UNV-X-STD-SFL  
Description: MRZ INTEGRAL LED DOWNLIGHT  
55 DEGREE WIDE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL 3  
Light Source: (1) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1087.0 lumens  
Efficiency: N/A  
Efficacy: 91.3 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.9  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219931

CATALOG NUMBER: MRZ-1-REC-X-3-L30-80-WFL-UNV-X-STD-SFL

### Luminous Intensity Polar Plot





TEST NUMBER: P219931

CATALOG NUMBER: MRZ-1-REC-X-3-L30-80-WFL-UNV-X-STD-SFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	69	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	538277
5°	534687
10°	514467
15°	474314
20°	427018
25°	376061
30°	305077
35°	223034
40°	152256
45°	100336
50°	65627
55°	41633
60°	26741
65°	16578
70°	12262
75°	8197
80°	3978
85°	0



TEST NUMBER: P219931

CATALOG NUMBER: MRZ-1-REC-X-3-L30-80-WFL-UNV-X-STD-SFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.3	9.3
10°-20°	259.1	23.8
20°-30°	313.1	28.8
30°-40°	233.0	21.4
40°-50°	114.8	10.6
50°-60°	45.3	4.2
60°-70°	15.6	1.4
70°-80°	4.7	0.4
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	673.5	62.0
0°-40°	906.4	83.4
0°-60°	1066.6	98.1
0°-90°	1087.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1087.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1091	
5°	1080	101
15°	929	259
25°	691	313
35°	370	233
45°	144	115
55°	48	45
65°	14	16
75°	4	5
85°	0	0
90°	0	



TEST NUMBER: P219931

CATALOG NUMBER: MRZ-1-REC-X-3-L30-80-WFL-UNV-X-STD-SFL

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1091.0
2.5°	1086.7
5°	1079.6
7.5°	1058.2
10°	1026.9
12.5°	981.3
15°	928.6
17.5°	870.2
20°	813.3
22.5°	756.3
25°	690.8
27.5°	616.7
30°	535.5
32.5°	451.5
35°	370.3
37.5°	299.1
40°	236.4
42.5°	185.2
45°	143.8
47.5°	111.1
50°	85.5
52.5°	64.1
55°	48.4
57.5°	35.6
60°	27.1
62.5°	19.9
65°	14.2
67.5°	11.4
70°	8.5
72.5°	5.7
75°	4.3
77.5°	2.8
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)