

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219752

Luminaire Tested: **MRZ-1-REC-X-4-L30-80-FL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219752  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14876)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-4-L30-80-FL-UNV-X-STD-HEX  
Description: MRZ INTEGRAL LED DOWNLIGHT  
40 DEGREE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 4  
Light Source: (1) 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 934.4 lumens  
Efficiency: N/A  
Efficacy: 59.1 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 15.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219752

CATALOG NUMBER: MRZ-1-REC-X-4-L30-80-FL-UNV-X-STD-HEX

### Luminous Intensity Polar Plot





TEST NUMBER: P219752

CATALOG NUMBER: MRZ-1-REC-X-4-L30-80-FL-UNV-X-STD-HEX

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	88	84	80	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	75
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69
10	83	76	71	68	83	75	71	68	75	71	68	74	70	68	73	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1277014
5°	1213348
10°	1049425
15°	787118
20°	490601
25°	257820
30°	116220
35°	44992
40°	17583
45°	8931
50°	4222
55°	3097
60°	1776
65°	2101
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219752

CATALOG NUMBER: MRZ-1-REC-X-4-L30-80-FL-UNV-X-STD-HEX

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	223.1	23.9
10°-20°	416.4	44.6
20°-30°	225.9	24.2
30°-40°	54.7	5.9
40°-50°	10.4	1.1
50°-60°	2.8	0.3
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	865.4	92.6
0°-40°	920.1	98.5
0°-60°	933.3	99.9
0°-90°	934.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	934.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2588	
5°	2450	223
15°	1541	416
25°	474	226
35°	75	55
45°	13	10
55°	4	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219752

CATALOG NUMBER: MRZ-1-REC-X-4-L30-80-FL-UNV-X-STD-HEX

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2588.3
2.5°	2540.9
5°	2449.9
7.5°	2313.3
10°	2094.7
12.5°	1836.0
15°	1541.0
17.5°	1225.8
20°	934.4
22.5°	675.8
25°	473.6
27.5°	318.8
30°	204.0
32.5°	125.7
35°	74.7
37.5°	45.5
40°	27.3
42.5°	18.2
45°	12.8
47.5°	7.3
50°	5.5
52.5°	3.6
55°	3.6
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)