

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866418

Luminaire Tested: PRLX-2004-M-927-15L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866418  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-56)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-927-15L-L-U-S-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,  
BELL WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 2  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 728.6 lumens  
Efficiency: N/A  
Efficacy: 52.0 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866418

CATALOG NUMBER: PRLX-2004-M-927-15L-L-U-S-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866418

CATALOG NUMBER: PRLX-2004-M-927-15L-L-U-S-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77
4	95	87	81	76	93	85	80	76	83	78	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57
8	76	66	59	55	75	65	59	55	64	59	55	63	58	54	62	57	54	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	51	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	5471
5°	5292
10°	5030
15°	4808
20°	4618
25°	4420
30°	4234
35°	3193
40°	1063
45°	394
50°	358
55°	327
60°	296
65°	273
70°	256
75°	246
80°	224
85°	210

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 394 cd/sqm

TEST NUMBER: P866418

CATALOG NUMBER: PRLX-2004-M-927-15L-L-U-S-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.0	8.5
10°-20°	164.4	22.6
20°-30°	232.0	31.8
30°-40°	187.5	25.7
40°-50°	35.9	4.9
50°-60°	21.2	2.9
60°-70°	14.5	2.0
70°-80°	8.4	1.2
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	458.4	62.9
0°-40°	645.9	88.7
0°-60°	703.0	96.5
0°-90°	728.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	728.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	688	
5°	663	62
15°	584	164
25°	504	232
35°	329	188
45°	35	36
55°	24	21
65°	14	14
75°	8	8
85°	2	3
90°	0	

TEST NUMBER: P866418

CATALOG NUMBER: PRLX-2004-M-927-15L-L-U-S-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	687.7
2.5°	681.6
5°	662.6
7.5°	641.7
10°	622.7
12.5°	602.9
15°	583.8
17.5°	565.2
20°	545.4
22.5°	525.2
25°	503.5
27.5°	483.0
30°	460.9
32.5°	420.2
35°	328.8
37.5°	194.1
40°	102.4
42.5°	57.5
45°	35.0
47.5°	30.8
50°	28.9
52.5°	26.3
55°	23.6
57.5°	21.3
60°	18.6
62.5°	16.7
65°	14.5
67.5°	12.6
70°	11.0
72.5°	9.5
75°	8.0
77.5°	6.5
80°	4.9
82.5°	3.8
85°	2.3
87.5°	1.1
90°	0.0

TEST NUMBER: P866418  
 CATALOG NUMBER: PRLX-2004-M-927-15L-L-U-S-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.87	3.92	3.23	4.23	4.54	2.87	3.92	3.23	4.23	4.54
	3H	4.33	5.26	4.72	5.59	5.96	4.33	5.26	4.72	5.59	5.96
	4H	4.94	5.80	5.35	6.15	6.54	4.94	5.80	5.35	6.15	6.54
	6H	5.40	6.18	5.82	6.56	6.96	5.40	6.18	5.82	6.56	6.96
	8H	5.56	6.30	6.00	6.70	7.10	5.56	6.30	6.00	6.70	7.10
	12H	5.67	6.38	6.10	6.76	7.19	5.67	6.38	6.10	6.76	7.19
4H	2H	3.29	4.15	3.70	4.50	4.89	3.29	4.15	3.70	4.50	4.89
	3H	4.99	5.69	5.40	6.10	6.51	4.99	5.69	5.40	6.10	6.51
	4H	5.73	6.36	6.17	6.78	7.23	5.73	6.36	6.17	6.78	7.23
	6H	6.32	6.86	6.79	7.31	7.78	6.32	6.86	6.79	7.31	7.78
	8H	6.53	7.03	7.01	7.48	7.96	6.53	7.03	7.01	7.48	7.96
	12H	6.68	7.12	7.17	7.61	8.08	6.68	7.12	7.17	7.61	8.08
8H	4H	5.95	6.46	6.43	6.91	7.38	5.95	6.46	6.43	6.91	7.38
	6H	6.68	7.08	7.19	7.58	8.07	6.68	7.08	7.19	7.58	8.07
	8H	6.99	7.34	7.52	7.86	8.36	6.99	7.34	7.52	7.86	8.36
	12H	7.23	7.54	7.75	8.04	8.62	7.23	7.54	7.75	8.04	8.62
12H	4H	5.96	6.39	6.45	6.88	7.36	5.96	6.39	6.45	6.88	7.36
	6H	6.72	7.08	7.25	7.60	8.09	6.72	7.08	7.25	7.60	8.09
	8H	7.09	7.40	7.61	7.90	8.48	7.09	7.40	7.61	7.90	8.48