

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219566

Luminaire Tested: **MRZ-1-REC-X-4-L30-80-NFL-UNV-X-STD**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14859)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-4-L30-80-NFL-UNV-X-STD
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC, LIGHT LEVEL 4
Light Source: (1) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1590.2 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.37
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219566

CATALOG NUMBER: MRZ-1-REC-X-4-L30-80-NFL-UNV-X-STD

Luminous Intensity Polar Plot





TEST NUMBER: P219566

CATALOG NUMBER: MRZ-1-REC-X-4-L30-80-NFL-UNV-X-STD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	81	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77
10	89	83	79	76	89	83	79	76	82	78	76	81	78	76	81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4058392
5°	3679664
10°	2694729
15°	1098748
20°	374881
25°	219115
30°	122430
35°	65832
40°	35166
45°	22886
50°	9825
55°	6279
60°	3552
65°	2101
70°	2597
75°	3431
80°	0
85°	0



TEST NUMBER: P219566

CATALOG NUMBER: MRZ-1-REC-X-4-L30-80-NFL-UNV-X-STD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	643.0	40.4
10°-20°	650.0	40.9
20°-30°	189.9	11.9
30°-40°	72.7	4.6
40°-50°	24.4	1.5
50°-60°	6.7	0.4
60°-70°	2.4	0.2
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1482.8	93.2
0°-40°	1555.5	97.8
0°-60°	1586.6	99.8
0°-90°	1590.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1590.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8226	
5°	7430	643
15°	2151	650
25°	402	190
35°	109	73
45°	33	24
55°	7	7
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P219566

CATALOG NUMBER: MRZ-1-REC-X-4-L30-80-NFL-UNV-X-STD

CANDELA DISTRIBUTION (FULL):

0°	
0°	8225.7
2.5°	8036.3
5°	7429.7
7.5°	6504.4
10°	5378.8
12.5°	3843.3
15°	2151.1
17.5°	1142.1
20°	714.0
22.5°	530.0
25°	402.5
27.5°	300.5
30°	214.9
32.5°	154.8
35°	109.3
37.5°	76.5
40°	54.6
42.5°	41.9
45°	32.8
47.5°	20.0
50°	12.8
52.5°	9.1
55°	7.3
57.5°	5.5
60°	3.6
62.5°	3.6
65°	1.8
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)