

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219555

Luminaire Tested: **MRZ-1-REC-X-2-L30-97-NFL-UNV-X-STD**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14859)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-2-L30-97-NFL-UNV-X-STD
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC, LIGHT LEVEL2
Light Source: (1) 3000K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 698.4 lumens
Efficiency: N/A
Efficacy: 79.4 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.37
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219555

CATALOG NUMBER: MRZ-1-REC-X-2-L30-97-NFL-UNV-X-STD

Luminous Intensity Polar Plot





TEST NUMBER: P219555

CATALOG NUMBER: MRZ-1-REC-X-2-L30-97-NFL-UNV-X-STD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99		100	99	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91		95	92	90		93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88		92	89	87		91	88	86	85
6	99	93	89	86	98	92	88	86	91	88	85		90	87	85		88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	83		87	84	82		86	84	82	81
8	94	87	83	81	93	87	83	81	86	83	80		85	82	80		84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78		83	80	78		82	80	78	77
10	89	83	79	76	89	83	79	76	82	78	76		81	78	76		81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1782235
5°	1615898
10°	1183390
15°	482538
20°	164654
25°	96247
30°	53780
35°	28911
40°	15457
45°	10048
50°	4298
55°	2753
60°	1579
65°	934
70°	1154
75°	1525
80°	0
85°	0



TEST NUMBER: P219555

CATALOG NUMBER: MRZ-1-REC-X-2-L30-97-NFL-UNV-X-STD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.4	40.4
10°-20°	285.4	40.9
20°-30°	83.4	11.9
30°-40°	31.9	4.6
40°-50°	10.7	1.5
50°-60°	2.9	0.4
60°-70°	1.1	0.2
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	651.2	93.2
0°-40°	683.1	97.8
0°-60°	696.8	99.8
0°-90°	698.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	698.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3612	
5°	3263	282
15°	945	285
25°	177	83
35°	48	32
45°	14	11
55°	3	3
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P219555

CATALOG NUMBER: MRZ-1-REC-X-2-L30-97-NFL-UNV-X-STD

CANDELA DISTRIBUTION (FULL):

0°	
0°	3612.3
2.5°	3529.1
5°	3262.7
7.5°	2856.4
10°	2362.1
12.5°	1687.8
15°	944.7
17.5°	501.5
20°	313.6
22.5°	232.8
25°	176.8
27.5°	132.0
30°	94.4
32.5°	68.0
35°	48.0
37.5°	33.6
40°	24.0
42.5°	18.4
45°	14.4
47.5°	8.8
50°	5.6
52.5°	4.0
55°	3.2
57.5°	2.4
60°	1.6
62.5°	1.6
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)