

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219934

Luminaire Tested: **MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219934  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14883)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-SFL  
Description: MRZ INTEGRAL LED DOWNLIGHT  
55 DEGREE WIDE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL 3  
Light Source: (1) 3000K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 834.5 lumens  
Efficiency: N/A  
Efficacy: 69.0 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.9  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 12.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219934

CATALOG NUMBER: MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-SFL

### Luminous Intensity Polar Plot





TEST NUMBER: P219934

CATALOG NUMBER: MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-SFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	69	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	413156
5°	410425
10°	394931
15°	364087
20°	327785
25°	288632
30°	234206
35°	171235
40°	116897
45°	77031
50°	50352
55°	31999
60°	20525
65°	12725
70°	9521
75°	6291
80°	3125
85°	0



TEST NUMBER: P219934

CATALOG NUMBER: MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-SFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.8	9.3
10°-20°	198.9	23.8
20°-30°	240.3	28.8
30°-40°	178.8	21.4
40°-50°	88.1	10.6
50°-60°	34.8	4.2
60°-70°	12.0	1.4
70°-80°	3.6	0.4
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.0	62.0
0°-40°	695.8	83.4
0°-60°	818.7	98.1
0°-90°	834.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	834.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	837	
5°	829	78
15°	713	199
25°	530	240
35°	284	179
45°	110	88
55°	37	35
65°	11	12
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P219934

CATALOG NUMBER: MRZ-1-REC-X-3-L30-97-WFL-UNV-X-STD-SFL

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	837.4
2.5°	834.2
5°	828.7
7.5°	812.3
10°	788.3
12.5°	753.3
15°	712.8
17.5°	668.0
20°	624.3
22.5°	580.5
25°	530.2
27.5°	473.4
30°	411.1
32.5°	346.6
35°	284.3
37.5°	229.6
40°	181.5
42.5°	142.1
45°	110.4
47.5°	85.3
50°	65.6
52.5°	49.2
55°	37.2
57.5°	27.3
60°	20.8
62.5°	15.3
65°	10.9
67.5°	8.7
70°	6.6
72.5°	4.4
75°	3.3
77.5°	2.2
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)