

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219663

Luminaire Tested: **MRZ-1-REC-X-4-L30-97-NFL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219663  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14873)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-4-L30-97-NFL-UNV-X-STD-SFL  
Description: MRZ INTEGRAL LED DOWNLIGHT  
25 DEGREE NARROW FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL 4  
Light Source: (1) 3000K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1173.6 lumens  
Efficiency: N/A  
Efficacy: 74.3 lumens/watt  
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.4  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 15.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219663

CATALOG NUMBER: MRZ-1-REC-X-4-L30-97-NFL-UNV-X-STD-SFL

### Luminous Intensity Polar Plot





TEST NUMBER: P219663

CATALOG NUMBER: MRZ-1-REC-X-4-L30-97-NFL-UNV-X-STD-SFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	95	98	95	93	96	94	92	94	92	90	89
4	103	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	85	90	87	85	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80
7	94	88	83	80	93	87	83	80	86	82	80	85	82	79	84	81	79	78
8	92	85	80	77	91	84	80	77	83	80	77	82	79	77	82	79	76	75
9	89	82	78	75	88	82	78	75	81	77	75	80	77	74	79	76	74	73
10	87	80	76	73	86	79	75	73	79	75	73	78	75	72	77	74	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2630996
5°	2400050
10°	1726665
15°	857709
20°	349416
25°	180409
30°	105965
35°	61495
40°	38708
45°	26375
50°	17193
55°	10838
60°	6907
65°	6538
70°	4039
75°	2669
80°	3978
85°	0



TEST NUMBER: P219663

CATALOG NUMBER: MRZ-1-REC-X-4-L30-97-NFL-UNV-X-STD-SFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	417.6	35.6
10°-20°	477.2	40.7
20°-30°	162.4	13.8
30°-40°	67.6	5.8
40°-50°	29.5	2.5
50°-60°	12.0	1.0
60°-70°	5.0	0.4
70°-80°	2.0	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1057.2	90.1
0°-40°	1124.9	95.8
0°-60°	1166.4	99.4
0°-90°	1173.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1173.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5333	
5°	4846	418
15°	1679	477
25°	331	162
35°	102	68
45°	38	30
55°	13	12
65°	6	5
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P219663

CATALOG NUMBER: MRZ-1-REC-X-4-L30-97-NFL-UNV-X-STD-SFL

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5332.6
2.5°	5215.2
5°	4846.0
7.5°	4240.6
10°	3446.5
12.5°	2547.5
15°	1679.2
17.5°	1037.4
20°	665.5
22.5°	451.6
25°	331.4
27.5°	247.5
30°	186.0
32.5°	138.4
35°	102.1
37.5°	76.9
40°	60.1
42.5°	46.1
45°	37.8
47.5°	29.4
50°	22.4
52.5°	16.8
55°	12.6
57.5°	9.8
60°	7.0
62.5°	5.6
65°	5.6
67.5°	4.2
70°	2.8
72.5°	2.8
75°	1.4
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)