

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P226142

Luminaire Tested: **MRZ-1-REC-X-1-L35-80-FL-UNV-X-STD**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P226142
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14875)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-1-L35-80-FL-UNV-X-STD
Description: MRZ INTEGRAL LED DOWNLIGHT
40 DEGREE FLOOD OPTIC, LIGHT LEVEL 1
Light Source: (1) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 629.3 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 5.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P226142

CATALOG NUMBER: MRZ-1-REC-X-1-L35-80-FL-UNV-X-STD

Luminous Intensity Polar Plot





TEST NUMBER: P226142

CATALOG NUMBER: MRZ-1-REC-X-1-L35-80-FL-UNV-X-STD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87	84	82	81
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77	73	71	69
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74	70	67	66
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71	67	64	63
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68	64	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	568176
5°	579211
10°	560709
15°	477941
20°	341068
25°	209588
30°	113144
35°	54388
40°	26342
45°	14025
50°	8213
55°	5505
60°	3552
65°	2452
70°	2020
75°	1334
80°	1989
85°	0



TEST NUMBER: P226142

CATALOG NUMBER: MRZ-1-REC-X-1-L35-80-FL-UNV-X-STD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.3	17.5
10°-20°	252.2	40.1
20°-30°	178.9	28.4
30°-40°	61.7	9.8
40°-50°	16.8	2.7
50°-60°	5.9	0.9
60°-70°	2.4	0.4
70°-80°	1.0	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	541.4	86.0
0°-40°	603.1	95.8
0°-60°	625.8	99.4
0°-90°	629.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	629.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1152	
5°	1170	110
15°	936	252
25°	385	179
35°	90	62
45°	20	17
55°	6	6
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P226142

CATALOG NUMBER: MRZ-1-REC-X-1-L35-80-FL-UNV-X-STD

CANDELA DISTRIBUTION (FULL):

0°	
0°	1151.6
2.5°	1156.6
5°	1169.5
7.5°	1165.9
10°	1119.2
12.5°	1042.6
15°	935.7
17.5°	794.5
20°	649.6
22.5°	510.5
25°	385.0
27.5°	279.7
30°	198.6
32.5°	134.8
35°	90.3
37.5°	60.3
40°	40.9
42.5°	27.9
45°	20.1
47.5°	14.4
50°	10.7
52.5°	7.9
55°	6.4
57.5°	5.0
60°	3.6
62.5°	2.9
65°	2.1
67.5°	2.1
70°	1.4
72.5°	1.4
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)