

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219800

Luminaire Tested: **MRZ-1-REC-X-2-L35-80-FL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219800  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14878)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-2-L35-80-FL-UNV-X-STD-SFL  
Description: MRZ INTEGRAL LED DOWNLIGHT  
40 DEGREE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL2  
Light Source: (1) 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 913.5 lumens  
Efficiency: N/A  
Efficacy: 103.8 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 8.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219800

CATALOG NUMBER: MRZ-1-REC-X-2-L35-80-FL-UNV-X-STD-SFL

### Luminous Intensity Polar Plot





TEST NUMBER: P219800

CATALOG NUMBER: MRZ-1-REC-X-2-L35-80-FL-UNV-X-STD-SFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94
2	109	105	101	98	107	103	99	97	100	97	95	97	94	93	94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	88	85	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75
6	91	83	78	74	90	83	78	74	81	77	73	80	76	73	79	75	73	71
7	88	79	74	70	86	79	74	70	77	73	70	76	72	69	75	72	69	68
8	84	76	70	67	83	75	70	66	74	69	66	73	69	66	72	68	66	64
9	81	72	67	63	80	72	67	63	71	66	63	70	66	63	69	65	63	61
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	804110
5°	804507
10°	766466
15°	648491
20°	475164
25°	304910
30°	173931
35°	92635
40°	49528
45°	28328
50°	17731
55°	12301
60°	8683
65°	6421
70°	4760
75°	4194
80°	3125
85°	0



TEST NUMBER: P219800

CATALOG NUMBER: MRZ-1-REC-X-2-L35-80-FL-UNV-X-STD-SFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.2	16.7
10°-20°	345.1	37.8
20°-30°	259.0	28.3
30°-40°	102.8	11.3
40°-50°	33.6	3.7
50°-60°	13.1	1.4
60°-70°	5.6	0.6
70°-80°	2.0	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	756.3	82.8
0°-40°	859.1	94.0
0°-60°	905.8	99.2
0°-90°	913.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	913.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1630	
5°	1624	152
15°	1270	345
25°	560	259
35°	154	103
45°	41	34
55°	14	13
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P219800

CATALOG NUMBER: MRZ-1-REC-X-2-L35-80-FL-UNV-X-STD-SFL

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1629.8
2.5°	1632.0
5°	1624.4
7.5°	1596.9
10°	1529.9
12.5°	1420.1
15°	1269.6
17.5°	1092.8
20°	905.0
22.5°	723.8
25°	560.1
27.5°	419.5
30°	305.3
32.5°	218.6
35°	153.8
37.5°	108.7
40°	76.9
42.5°	56.0
45°	40.6
47.5°	29.7
50°	23.1
52.5°	17.6
55°	14.3
57.5°	11.0
60°	8.8
62.5°	6.6
65°	5.5
67.5°	4.4
70°	3.3
72.5°	2.2
75°	2.2
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)