

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866481

Luminaire Tested: PRLX-2004-M-930-15L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866481  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-55)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-930-15L-L-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,  
BELL WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 2  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 770.0 lumens  
Efficiency: N/A  
Efficacy: 55.0 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866481

CATALOG NUMBER: PRLX-2004-M-930-15L-L-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866481

CATALOG NUMBER: PRLX-2004-M-930-15L-L-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99		100	98	97		96	95	94	92
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84	81	79	77
4	95	86	80	76	93	85	80	75	83	78	74		81	77	74		79	76	73	71
5	90	80	74	69	88	79	73	69	78	72	68		76	71	68		74	70	67	66
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70	66	62	61
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62	57	54	52
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	47		56	51	47		55	50	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	5738
5°	5538
10°	5263
15°	5044
20°	4854
25°	4654
30°	4456
35°	3356
40°	1131
45°	440
50°	390
55°	359
60°	329
65°	301
70°	279
75°	271
80°	257
85°	256

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 440 cd/sqm

TEST NUMBER: P866481

CATALOG NUMBER: PRLX-2004-M-930-15L-L-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.9	8.4
10°-20°	172.5	22.4
20°-30°	244.2	31.7
30°-40°	198.1	25.7
40°-50°	38.9	5.1
50°-60°	23.2	3.0
60°-70°	16.0	2.1
70°-80°	9.3	1.2
80°-90°	2.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.5	62.5
0°-40°	679.7	88.3
0°-60°	741.7	96.3
0°-90°	770.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	721	
5°	693	65
15°	612	172
25°	530	244
35°	346	198
45°	39	39
55°	26	23
65°	16	16
75°	9	9
85°	3	3
90°	0	

TEST NUMBER: P866481

CATALOG NUMBER: PRLX-2004-M-930-15L-L-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	721.3
2.5°	714.5
5°	693.4
7.5°	671.8
10°	651.5
12.5°	631.9
15°	612.4
17.5°	593.2
20°	573.3
22.5°	551.7
25°	530.2
27.5°	509.1
30°	485.1
32.5°	441.2
35°	345.5
37.5°	209.8
40°	108.9
42.5°	61.4
45°	39.1
47.5°	33.9
50°	31.5
52.5°	28.7
55°	25.9
57.5°	23.1
60°	20.7
62.5°	18.4
65°	16.0
67.5°	14.0
70°	12.0
72.5°	10.4
75°	8.8
77.5°	7.2
80°	5.6
82.5°	4.0
85°	2.8
87.5°	1.2
90°	0.0



TEST NUMBER: P866481  
 CATALOG NUMBER: PRLX-2004-M-930-15L-L-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	3.24	4.30	3.61	4.61	4.93	3.24	4.30	3.61	4.61	4.93
	3H	4.75	5.68	5.13	6.02	6.38	4.75	5.68	5.13	6.02	6.38
	4H	5.36	6.23	5.77	6.58	6.97	5.36	6.23	5.77	6.58	6.97
	6H	5.85	6.64	6.26	7.01	7.41	5.85	6.64	6.26	7.01	7.41
	8H	6.01	6.75	6.44	7.14	7.55	6.01	6.75	6.44	7.14	7.55
	12H	6.12	6.84	6.56	7.22	7.65	6.12	6.84	6.56	7.22	7.65
4H	2H	3.69	4.55	4.09	4.91	5.29	3.69	4.55	4.09	4.91	5.29
	3H	5.41	6.12	5.83	6.53	6.94	5.41	6.12	5.83	6.53	6.94
	4H	6.16	6.80	6.60	7.22	7.67	6.16	6.80	6.60	7.22	7.67
	6H	6.78	7.33	7.25	7.77	8.25	6.78	7.33	7.25	7.77	8.25
	8H	6.99	7.49	7.46	7.94	8.42	6.99	7.49	7.46	7.94	8.42
	12H	7.16	7.60	7.65	8.08	8.56	7.16	7.60	7.65	8.08	8.56
8H	4H	6.39	6.90	6.87	7.35	7.83	6.39	6.90	6.87	7.35	7.83
	6H	7.16	7.56	7.66	8.06	8.55	7.16	7.56	7.66	8.06	8.55
	8H	7.45	7.81	7.98	8.33	8.83	7.45	7.81	7.98	8.33	8.83
	12H	7.72	8.03	8.24	8.53	9.11	7.72	8.03	8.24	8.53	9.11
12H	4H	6.40	6.84	6.89	7.33	7.80	6.40	6.84	6.89	7.33	7.80
	6H	7.20	7.56	7.73	8.08	8.57	7.20	7.56	7.73	8.08	8.57
	8H	7.55	7.86	8.07	8.36	8.94	7.55	7.86	8.07	8.36	8.94