

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219715

Luminaire Tested: **MRZ-1-REC-X-3-L35-80-FL-UNV-X-STD**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219715  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14875)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-3-L35-80-FL-UNV-X-STD  
Description: MRZ INTEGRAL LED DOWNLIGHT  
40 DEGREE FLOOD OPTIC, LIGHT LEVEL 3  
Light Source: (1) 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1317.4 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219715

CATALOG NUMBER: MRZ-1-REC-X-3-L35-80-FL-UNV-X-STD

### Luminous Intensity Polar Plot





TEST NUMBER: P219715

CATALOG NUMBER: MRZ-1-REC-X-3-L35-80-FL-UNV-X-STD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87	84	82	81
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77	73	71	69
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74	70	67	66
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71	67	64	63
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68	64	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1189439
5°	1212555
10°	1173921
15°	1000626
20°	714059
25°	438828
30°	236884
35°	113896
40°	55132
45°	29305
50°	17270
55°	11612
60°	7401
65°	5253
70°	4328
75°	2859
80°	4262
85°	0



TEST NUMBER: P219715

CATALOG NUMBER: MRZ-1-REC-X-3-L35-80-FL-UNV-X-STD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	230.8	17.5
10°-20°	528.1	40.1
20°-30°	374.5	28.4
30°-40°	129.2	9.8
40°-50°	35.1	2.7
50°-60°	12.3	0.9
60°-70°	5.0	0.4
70°-80°	2.2	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1133.4	86.0
0°-40°	1262.6	95.8
0°-60°	1310.1	99.4
0°-90°	1317.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1317.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2411	
5°	2448	231
15°	1959	528
25°	806	375
35°	189	129
45°	42	35
55°	14	12
65°	4	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P219715

CATALOG NUMBER: MRZ-1-REC-X-3-L35-80-FL-UNV-X-STD

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2410.8
2.5°	2421.3
5°	2448.3
7.5°	2440.8
10°	2343.2
12.5°	2182.6
15°	1959.0
17.5°	1663.2
20°	1360.0
22.5°	1068.8
25°	806.1
27.5°	585.4
30°	415.8
32.5°	282.2
35°	189.1
37.5°	126.1
40°	85.6
42.5°	58.5
45°	42.0
47.5°	30.0
50°	22.5
52.5°	16.5
55°	13.5
57.5°	10.5
60°	7.5
62.5°	6.0
65°	4.5
67.5°	4.5
70°	3.0
72.5°	3.0
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)