

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866487

Luminaire Tested: PRLX-2004-M-930-25L-G-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866487  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-42)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-930-25L-G-U-S-X-X-WHHR-X  
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS, BELL WITH WHITE INTERIOR SHADE.  
LIGHT LEVEL 3  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1499.7 lumens  
Efficiency: N/A  
Efficacy: 69.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.2  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866487

CATALOG NUMBER: PRLX-2004-M-930-25L-G-U-S-X-X-WHHR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866487

CATALOG NUMBER: PRLX-2004-M-930-25L-G-U-S-X-X-WHHR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	94	84	77	71	91	83	76	70	80	74	69	77	72	68	75	70	67	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57
5	80	69	60	54	78	67	60	54	65	59	53	64	58	53	62	57	52	50
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37
9	61	49	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	5681
5°	5698
10°	5710
15°	5701
20°	5680
25°	5615
30°	5320
35°	4824
40°	4267
45°	3703
50°	3152
55°	2646
60°	2360
65°	2191
70°	2056
75°	1961
80°	1888
85°	1817

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3703 cd/sqm

TEST NUMBER: P866487

CATALOG NUMBER: PRLX-2004-M-930-25L-G-U-S-X-X-WHHR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.9	4.5
10°-20°	195.4	13.0
20°-30°	292.1	19.5
30°-40°	310.0	20.7
40°-50°	254.6	17.0
50°-60°	174.2	11.6
60°-70°	115.8	7.7
70°-80°	67.8	4.5
80°-90°	22.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	555.4	37.0
0°-40°	865.3	57.7
0°-60°	1294.1	86.3
0°-90°	1499.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1499.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	714	
5°	714	68
15°	692	195
25°	640	292
35°	497	310
45°	329	255
55°	191	174
65°	116	116
75°	64	68
85°	20	22
90°	0	

TEST NUMBER: P866487

CATALOG NUMBER: PRLX-2004-M-930-25L-G-U-S-X-X-WHHR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	714.1
2.5°	714.1
5°	713.5
7.5°	710.8
10°	706.8
12.5°	700.8
15°	692.2
17.5°	682.9
20°	670.9
22.5°	657.6
25°	639.6
27.5°	612.4
30°	579.1
32.5°	541.2
35°	496.7
37.5°	454.1
40°	410.9
42.5°	369.0
45°	329.1
47.5°	292.6
50°	254.7
52.5°	220.8
55°	190.8
57.5°	167.6
60°	148.3
62.5°	131.7
65°	116.4
67.5°	101.7
70°	88.4
72.5°	75.8
75°	63.8
77.5°	52.5
80°	41.2
82.5°	30.6
85°	19.9
87.5°	10.0
90°	0.0

TEST NUMBER: P866487

CATALOG NUMBER: PRLX-2004-M-930-25L-G-U-S-X-X-WHHR-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.17	15.64	14.53	15.95	16.27	14.17	15.64	14.53	15.95	16.27
	3H	15.75	17.07	16.12	17.40	17.76	15.75	17.07	16.12	17.40	17.76
	4H	16.39	17.62	16.79	17.97	18.35	16.39	17.62	16.79	17.97	18.35
	6H	16.91	18.05	17.32	18.42	18.81	16.91	18.05	17.32	18.42	18.81
	8H	17.10	18.19	17.53	18.58	18.98	17.10	18.19	17.53	18.58	18.98
	12H	17.24	18.28	17.67	18.66	19.09	17.24	18.28	17.67	18.66	19.09
4H	2H	14.69	15.93	15.09	16.28	16.66	14.69	15.93	15.09	16.28	16.66
	3H	16.51	17.54	16.92	17.94	18.34	16.51	17.54	16.92	17.94	18.34
	4H	17.29	18.21	17.72	18.63	19.07	17.29	18.21	17.72	18.63	19.07
	6H	17.95	18.76	18.41	19.20	19.66	17.95	18.76	18.41	19.20	19.66
	8H	18.20	18.96	18.67	19.40	19.87	18.20	18.96	18.67	19.40	19.87
	12H	18.40	19.07	18.88	19.55	20.02	18.40	19.07	18.88	19.55	20.02
8H	4H	17.58	18.34	18.05	18.78	19.25	17.58	18.34	18.05	18.78	19.25
	6H	18.39	19.01	18.88	19.50	19.98	18.39	19.01	18.88	19.50	19.98
	8H	18.72	19.28	19.24	19.79	20.28	18.72	19.28	19.24	19.79	20.28
	12H	19.01	19.51	19.52	20.00	20.57	19.01	19.51	19.52	20.00	20.57
12H	4H	17.61	18.29	18.10	18.76	19.24	17.61	18.29	18.10	18.76	19.24
	6H	18.45	19.01	18.97	19.52	20.01	18.45	19.01	18.97	19.52	20.01
	8H	18.85	19.35	19.36	19.84	20.41	18.85	19.35	19.36	19.84	20.41