

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219591

Luminaire Tested: **MRZ-1-REC-X-3-L35-80-NFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219591
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14871)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-3-L35-80-NFL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 3
Light Source: (1) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 909.3 lumens
Efficiency: N/A
Efficacy: 76.4 lumens/watt
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.35
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219591

CATALOG NUMBER: MRZ-1-REC-X-3-L35-80-NFL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P219591

CATALOG NUMBER: MRZ-1-REC-X-3-L35-80-NFL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95
3	109	105	101	99	107	103	100	98	101	99	97	99	97	95	97	95	94	92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88
6	101	95	92	89	100	95	91	89	93	90	88	92	90	88	91	89	87	86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84
8	96	91	87	84	95	90	87	84	89	86	84	88	86	84	88	85	83	82
9	94	88	85	82	94	88	85	82	87	84	82	87	84	82	86	83	82	81
10	92	87	83	81	92	86	83	81	86	82	80	85	82	80	84	82	80	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2995801
5°	2525501
10°	1649963
15°	581936
20°	187598
25°	97227
30°	45349
35°	20780
40°	9661
45°	5233
50°	2303
55°	1290
60°	1480
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219591

CATALOG NUMBER: MRZ-1-REC-X-3-L35-80-NFL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	428.9	47.2
10°-20°	362.9	39.9
20°-30°	85.2	9.4
30°-40°	23.9	2.6
40°-50°	6.0	0.7
50°-60°	1.8	0.2
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	877.1	96.5
0°-40°	901.0	99.1
0°-60°	908.8	99.9
0°-90°	909.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	909.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6072	
5°	5099	429
15°	1139	363
25°	179	85
35°	34	24
45°	8	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219591

CATALOG NUMBER: MRZ-1-REC-X-3-L35-80-NFL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

	0°
0°	6072.0
2.5°	5791.3
5°	5099.3
7.5°	4222.6
10°	3293.4
12.5°	2188.6
15°	1139.3
17.5°	588.4
20°	357.3
22.5°	247.7
25°	178.6
27.5°	123.1
30°	79.6
32.5°	52.5
35°	34.5
37.5°	22.5
40°	15.0
42.5°	10.5
45°	7.5
47.5°	4.5
50°	3.0
52.5°	3.0
55°	1.5
57.5°	1.5
60°	1.5
62.5°	1.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)