

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219598

Luminaire Tested: **MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219598
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14871)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 4
Light Source: (1) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1162.9 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.35
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219598

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P219598

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95	95	95
3	109	105	101	99	107	103	100	98	101	99	97	99	97	95	97	95	94	92	92	92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90	90	90
5	103	98	94	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88	88	88
6	101	95	92	89	100	95	91	89	93	90	88	92	90	88	91	89	87	86	86	86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84	84	84
8	96	91	87	84	95	90	87	84	89	86	84	88	86	84	88	85	83	82	82	82
9	94	88	85	82	94	88	85	82	87	84	82	87	84	82	86	83	82	81	81	81
10	92	87	83	81	92	86	83	81	86	82	80	85	82	80	84	82	80	79	79	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3831290
5°	3229816
10°	2110123
15°	744264
20°	239892
25°	124337
30°	57939
35°	26622
40°	12366
45°	6698
50°	2917
55°	1634
60°	1875
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219598

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	548.5	47.2
10°-20°	464.2	39.9
20°-30°	109.0	9.4
30°-40°	30.5	2.6
40°-50°	7.6	0.7
50°-60°	2.3	0.2
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1121.7	96.5
0°-40°	1152.2	99.1
0°-60°	1162.2	99.9
0°-90°	1162.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1162.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7765	
5°	6521	549
15°	1457	464
25°	228	109
35°	44	31
45°	10	8
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219598

CATALOG NUMBER: MRZ-1-REC-X-4-L35-80-NFL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

0°	
0°	7765.4
2.5°	7406.4
5°	6521.4
7.5°	5400.2
10°	4211.9
12.5°	2799.0
15°	1457.1
17.5°	752.5
20°	456.9
22.5°	316.8
25°	228.4
27.5°	157.4
30°	101.7
32.5°	67.2
35°	44.2
37.5°	28.8
40°	19.2
42.5°	13.4
45°	9.6
47.5°	5.8
50°	3.8
52.5°	3.8
55°	1.9
57.5°	1.9
60°	1.9
62.5°	1.9
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)