

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866501

Luminaire Tested: PRLX-2004-M-930-45L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866501  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-43)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-930-45L-G-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,  
BELL WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 5  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 892.4 lumens  
Efficiency: N/A  
Efficacy: 23.0 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 38.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866501

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866501

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	75	81	77	74	72
4	91	82	75	70	89	81	74	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4446
5°	4444
10°	4429
15°	4397
20°	4317
25°	4213
30°	4013
35°	3522
40°	2884
45°	2141
50°	1378
55°	748
60°	552
65°	473
70°	419
75°	369
80°	330
85°	329

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2141 cd/sqm

TEST NUMBER: P866501

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.8	5.9
10°-20°	150.3	16.8
20°-30°	220.1	24.7
30°-40°	224.8	25.2
40°-50°	146.9	16.5
50°-60°	54.6	6.1
60°-70°	25.4	2.8
70°-80°	13.1	1.5
80°-90°	4.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.2	47.4
0°-40°	648.0	72.6
0°-60°	849.6	95.2
0°-90°	892.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	892.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	559	
5°	556	53
15°	534	150
25°	480	220
35°	363	225
45°	190	147
55°	54	55
65°	25	25
75°	12	13
85°	4	4
90°	0	

TEST NUMBER: P866501

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	558.9
2.5°	557.7
5°	556.5
7.5°	552.9
10°	548.2
12.5°	542.2
15°	533.8
17.5°	523.0
20°	509.9
22.5°	495.5
25°	479.9
27.5°	462.0
30°	436.8
32.5°	403.3
35°	362.6
37.5°	320.8
40°	277.7
42.5°	233.4
45°	190.3
47.5°	149.6
50°	111.3
52.5°	79.0
55°	53.9
57.5°	40.7
60°	34.7
62.5°	29.9
65°	25.1
67.5°	21.5
70°	18.0
72.5°	15.6
75°	12.0
77.5°	9.6
80°	7.2
82.5°	6.0
85°	3.6
87.5°	2.4
90°	0.0

TEST NUMBER: P866501  
 CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.39	7.65	6.75	7.96	8.28	6.39	7.65	6.75	7.96	8.28
	3H	7.58	8.69	7.96	9.02	9.39	7.58	8.69	7.96	9.02	9.39
	4H	8.02	9.06	8.43	9.41	9.79	8.02	9.06	8.43	9.41	9.79
	6H	8.33	9.28	8.75	9.65	10.05	8.33	9.28	8.75	9.65	10.05
	8H	8.46	9.36	8.89	9.75	10.15	8.46	9.36	8.89	9.75	10.15
	12H	8.55	9.41	8.98	9.79	10.22	8.55	9.41	8.98	9.79	10.22
4H	2H	6.76	7.79	7.16	8.14	8.52	6.76	7.79	7.16	8.14	8.52
	3H	8.17	9.01	8.59	9.42	9.82	8.17	9.01	8.59	9.42	9.82
	4H	8.72	9.47	9.15	9.89	10.33	8.72	9.47	9.15	9.89	10.33
	6H	9.14	9.79	9.61	10.24	10.71	9.14	9.79	9.61	10.24	10.71
	8H	9.32	9.93	9.79	10.37	10.85	9.32	9.93	9.79	10.37	10.85
	12H	9.46	9.99	9.94	10.47	10.95	9.46	9.99	9.94	10.47	10.95
8H	4H	8.88	9.49	9.35	9.94	10.41	8.88	9.49	9.35	9.94	10.41
	6H	9.42	9.91	9.92	10.41	10.89	9.42	9.91	9.92	10.41	10.89
	8H	9.68	10.13	10.21	10.64	11.14	9.68	10.13	10.21	10.64	11.14
	12H	9.90	10.30	10.42	10.79	11.36	9.90	10.30	10.42	10.79	11.36
12H	4H	8.88	9.41	9.37	9.90	10.37	8.88	9.41	9.37	9.90	10.37
	6H	9.44	9.89	9.97	10.41	10.90	9.44	9.89	9.97	10.41	10.90
	8H	9.77	10.16	10.29	10.66	11.23	9.77	10.16	10.29	10.66	11.23