

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P226160

Luminaire Tested: **MRZ-1-REC-X-1-L35-97-NFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P226160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14871)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-1-L35-97-NFL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 1
Light Source: (1) 3500K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 330.6 lumens
Efficiency: N/A
Efficacy: 61.2 lumens/watt
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.35
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 5.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P226160

CATALOG NUMBER: MRZ-1-REC-X-1-L35-97-NFL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P226160

CATALOG NUMBER: MRZ-1-REC-X-1-L35-97-NFL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95
3	109	105	101	99	107	103	100	98	101	99	97	99	97	95	97	95	94	92
4	106	101	98	95	105	100	97	94	98	95	93	96	94	92	95	93	91	90
5	103	98	94	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88
6	101	95	92	89	100	95	91	89	93	90	88	92	90	88	91	89	87	86
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84
8	96	91	87	84	95	90	87	84	89	86	84	88	86	84	88	85	83	82
9	94	88	85	82	94	88	85	82	87	84	82	87	84	82	86	83	82	81
10	92	87	83	81	92	86	83	81	86	82	80	85	82	80	84	82	80	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1089382
5°	918319
10°	599936
15°	211618
20°	68203
25°	35385
30°	16464
35°	7589
40°	3478
45°	1954
50°	844
55°	430
60°	493
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P226160

CATALOG NUMBER: MRZ-1-REC-X-1-L35-97-NFL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.0	47.2
10°-20°	132.0	39.9
20°-30°	31.0	9.4
30°-40°	8.7	2.6
40°-50°	2.2	0.7
50°-60°	0.6	0.2
60°-70°	0.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	318.9	96.5
0°-40°	327.6	99.1
0°-60°	330.4	99.9
0°-90°	330.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	330.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2208	
5°	1854	156
15°	414	132
25°	65	31
35°	13	9
45°	3	2
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P226160

CATALOG NUMBER: MRZ-1-REC-X-1-L35-97-NFL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

0°	
0°	2208.0
2.5°	2105.8
5°	1854.2
7.5°	1535.4
10°	1197.5
12.5°	795.8
15°	414.3
17.5°	214.0
20°	129.9
22.5°	90.1
25°	65.0
27.5°	44.7
30°	28.9
32.5°	19.1
35°	12.6
37.5°	8.2
40°	5.4
42.5°	3.8
45°	2.8
47.5°	1.6
50°	1.1
52.5°	1.1
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)