

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866524

Luminaire Tested: PRLX-2004-M-930-75L-G-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866524  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-45)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-930-75L-G-U-S-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,  
BELL WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 8  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 973.6 lumens  
Efficiency: N/A  
Efficacy: 14.0 lumens/watt  
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.18  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 69.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866524

CATALOG NUMBER: PRLX-2004-M-930-75L-G-U-S-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866524

CATALOG NUMBER: PRLX-2004-M-930-75L-G-U-S-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	107	105	102	103	101	99		99	98	96		96	95	94	92
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89	87	85	83
3	99	92	86	82	97	91	85	81	88	83	80		85	82	78		83	80	77	75
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77	73	70	68
5	88	78	71	66	86	77	70	66	75	69	65		73	68	65		72	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66	62	58	57
7	77	66	59	55	76	66	59	54	64	58	54		63	58	54		62	57	53	52
8	73	62	55	50	71	61	54	50	60	54	50		59	53	49		58	53	49	48
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	64	53	47	42	63	53	47	42	52	46	42		51	46	42		50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4936
5°	4939
10°	4963
15°	4978
20°	4982
25°	5026
30°	4966
35°	4378
40°	3480
45°	2401
50°	1259
55°	250
60°	127
65°	113
70°	93
75°	61
80°	92
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2401 cd/sqm

TEST NUMBER: P866524

CATALOG NUMBER: PRLX-2004-M-930-75L-G-U-S-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.9	6.0
10°-20°	170.6	17.5
20°-30°	263.3	27.0
30°-40°	277.7	28.5
40°-50°	164.2	16.9
50°-60°	29.9	3.1
60°-70°	5.4	0.6
70°-80°	2.9	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	492.8	50.6
0°-40°	770.4	79.1
0°-60°	964.5	99.1
0°-90°	973.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	973.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	620	
5°	618	59
15°	604	171
25°	572	263
35°	451	278
45°	213	164
55°	18	30
65°	6	5
75°	2	3
85°	0	1
90°	0	

TEST NUMBER: P866524

CATALOG NUMBER: PRLX-2004-M-930-75L-G-U-S-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	620.4
2.5°	620.4
5°	618.4
7.5°	616.4
10°	614.4
12.5°	610.4
15°	604.4
17.5°	596.4
20°	588.5
22.5°	580.5
25°	572.5
27.5°	562.5
30°	540.6
32.5°	500.7
35°	450.8
37.5°	395.0
40°	335.1
42.5°	273.3
45°	213.4
47.5°	155.6
50°	101.7
52.5°	53.9
55°	18.0
57.5°	10.0
60°	8.0
62.5°	6.0
65°	6.0
67.5°	4.0
70°	4.0
72.5°	4.0
75°	2.0
77.5°	2.0
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0



TEST NUMBER: P866524  
 CATALOG NUMBER: PRLX-2004-M-930-75L-G-U-S-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.13	0.00	0.00	0.00	0.00	0.13
	8H	0.00	0.00	0.00	0.00	0.47	0.00	0.00	0.00	0.00	0.47
	12H	0.00	0.00	0.00	0.03	0.50	0.00	0.00	0.00	0.03	0.50
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.35	0.00	0.00	0.00	0.00	0.35
	8H	0.00	0.00	0.00	0.37	0.86	0.00	0.00	0.00	0.37	0.86
	12H	0.00	0.00	0.06	0.39	0.96	0.00	0.00	0.06	0.39	0.96
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.42	0.00	0.00	0.00	0.00	0.42
	8H	0.00	0.00	0.11	0.44	1.01	0.00	0.00	0.11	0.44	1.01