

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219804

Luminaire Tested: **MRZ-1-REC-X-2-L35-97-FL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219804  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14878)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-2-L35-97-FL-UNV-X-STD-SFL  
Description: MRZ INTEGRAL LED DOWNLIGHT  
40 DEGREE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL2  
Light Source: (1) 3500K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 695.4 lumens  
Efficiency: N/A  
Efficacy: 79.0 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 8.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219804

CATALOG NUMBER: MRZ-1-REC-X-2-L35-97-FL-UNV-X-STD-SFL

### Luminous Intensity Polar Plot





TEST NUMBER: P219804

CATALOG NUMBER: MRZ-1-REC-X-2-L35-97-FL-UNV-X-STD-SFL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94
2	109	105	101	98	107	103	99	97	100	97	95	97	94	93	94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	88	85	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75
6	91	83	78	74	90	83	78	74	81	77	73	80	76	73	79	75	73	71
7	88	79	74	70	86	79	74	70	77	73	70	76	72	69	75	72	69	68
8	84	76	70	67	83	75	70	66	74	69	66	73	69	66	72	68	66	64
9	81	72	67	63	80	72	67	63	71	66	63	70	66	63	69	65	63	61
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	612136
5°	612444
10°	583504
15°	493673
20°	361703
25°	232125
30°	132400
35°	70530
40°	37678
45°	21560
50°	13509
55°	9376
60°	6611
65°	4903
70°	3606
75°	3241
80°	2273
85°	0



TEST NUMBER: P219804

CATALOG NUMBER: MRZ-1-REC-X-2-L35-97-FL-UNV-X-STD-SFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.9	16.7
10°-20°	262.7	37.8
20°-30°	197.1	28.3
30°-40°	78.3	11.3
40°-50°	25.5	3.7
50°-60°	10.0	1.4
60°-70°	4.2	0.6
70°-80°	1.5	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	575.8	82.8
0°-40°	654.0	94.0
0°-60°	689.5	99.2
0°-90°	695.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1241	
5°	1237	116
15°	966	263
25°	426	197
35°	117	78
45°	31	26
55°	11	10
65°	4	4
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P219804

CATALOG NUMBER: MRZ-1-REC-X-2-L35-97-FL-UNV-X-STD-SFL

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1240.7
2.5°	1242.4
5°	1236.6
7.5°	1215.7
10°	1164.7
12.5°	1081.0
15°	966.5
17.5°	831.9
20°	688.9
22.5°	551.0
25°	426.4
27.5°	319.4
30°	232.4
32.5°	166.4
35°	117.1
37.5°	82.8
40°	58.5
42.5°	42.6
45°	30.9
47.5°	22.6
50°	17.6
52.5°	13.4
55°	10.9
57.5°	8.4
60°	6.7
62.5°	5.0
65°	4.2
67.5°	3.3
70°	2.5
72.5°	1.7
75°	1.7
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)