

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219811

Luminaire Tested: **MRZ-1-REC-X-3-L35-97-FL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219811
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14878)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-3-L35-97-FL-UNV-X-STD-SFL
Description: MRZ INTEGRAL LED DOWNLIGHT
40 DEGREE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL 3
Light Source: (1) 3500K CCT, 97 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 950.5 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219811

CATALOG NUMBER: MRZ-1-REC-X-3-L35-97-FL-UNV-X-STD-SFL

Luminous Intensity Polar Plot





TEST NUMBER: P219811

CATALOG NUMBER: MRZ-1-REC-X-3-L35-97-FL-UNV-X-STD-SFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94
2	109	105	101	98	107	103	99	97	100	97	95	97	94	93	94	92	91	89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	88	85	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75
6	91	83	78	74	90	83	78	74	81	77	73	80	76	73	79	75	73	71
7	88	79	74	70	86	79	74	70	77	73	70	76	72	69	75	72	69	68
8	84	76	70	67	83	75	70	66	74	69	66	73	69	66	72	68	66	64
9	81	72	67	63	80	72	67	63	71	66	63	70	66	63	69	65	63	61
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	836673
5°	837046
10°	797477
15°	674746
20°	494381
25°	317267
30°	180995
35°	96369
40°	51525
45°	29515
50°	18421
55°	12817
60°	8980
65°	6654
70°	4905
75°	4384
80°	3125
85°	0



TEST NUMBER: P219811

CATALOG NUMBER: MRZ-1-REC-X-3-L35-97-FL-UNV-X-STD-SFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	16.7
10°-20°	359.1	37.8
20°-30°	269.5	28.3
30°-40°	107.0	11.3
40°-50°	34.9	3.7
50°-60°	13.6	1.4
60°-70°	5.8	0.6
70°-80°	2.1	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	786.9	82.8
0°-40°	893.9	94.0
0°-60°	942.4	99.2
0°-90°	950.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	950.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1696	
5°	1690	158
15°	1321	359
25°	583	269
35°	160	107
45°	42	35
55°	15	14
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P219811

CATALOG NUMBER: MRZ-1-REC-X-3-L35-97-FL-UNV-X-STD-SFL

CANDELA DISTRIBUTION (FULL):

0°	
0°	1695.8
2.5°	1698.1
5°	1690.1
7.5°	1661.5
10°	1591.8
12.5°	1477.6
15°	1321.0
17.5°	1137.0
20°	941.6
22.5°	753.1
25°	582.8
27.5°	436.5
30°	317.7
32.5°	227.4
35°	160.0
37.5°	113.1
40°	80.0
42.5°	58.3
45°	42.3
47.5°	30.9
50°	24.0
52.5°	18.3
55°	14.9
57.5°	11.4
60°	9.1
62.5°	6.9
65°	5.7
67.5°	4.6
70°	3.4
72.5°	2.3
75°	2.3
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)