

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866543

Luminaire Tested: PRLX-2004-M-935-15L-G-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866543  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-42)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-935-15L-G-U-S-X-X-WHHR-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,  
BELL WITH WHITE INTERIOR SHADE.  
LIGHT LEVEL 2  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 918.1 lumens  
Efficiency: N/A  
Efficacy: 65.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.2  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866543

CATALOG NUMBER: PRLX-2004-M-935-15L-G-U-S-X-X-WHHR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866543

CATALOG NUMBER: PRLX-2004-M-935-15L-G-U-S-X-X-WHHR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	94	84	77	71	91	83	76	70	80	74	69	77	72	68	75	70	67	65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57
5	80	69	60	54	78	67	60	54	65	59	53	64	58	53	62	57	52	50
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37
9	61	49	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3478
5°	3488
10°	3496
15°	3490
20°	3477
25°	3438
30°	3257
35°	2953
40°	2612
45°	2267
50°	1930
55°	1620
60°	1445
65°	1340
70°	1258
75°	1202
80°	1155
85°	1114

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2267 cd/sqm

TEST NUMBER: P866543

CATALOG NUMBER: PRLX-2004-M-935-15L-G-U-S-X-X-WHHR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.6	4.5
10°-20°	119.6	13.0
20°-30°	178.8	19.5
30°-40°	189.8	20.7
40°-50°	155.9	17.0
50°-60°	106.6	11.6
60°-70°	70.9	7.7
70°-80°	41.5	4.5
80°-90°	13.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.0	37.0
0°-40°	529.7	57.7
0°-60°	792.2	86.3
0°-90°	918.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	918.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	437	
5°	437	42
15°	424	120
25°	392	179
35°	304	190
45°	202	156
55°	117	107
65°	71	71
75°	39	42
85°	12	13
90°	0	

TEST NUMBER: P866543

CATALOG NUMBER: PRLX-2004-M-935-15L-G-U-S-X-X-WHHR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	437.2
2.5°	437.2
5°	436.7
7.5°	435.1
10°	432.7
12.5°	429.0
15°	423.7
17.5°	418.0
20°	410.7
22.5°	402.6
25°	391.6
27.5°	374.9
30°	354.5
32.5°	331.3
35°	304.1
37.5°	278.0
40°	251.5
42.5°	225.9
45°	201.5
47.5°	179.1
50°	155.9
52.5°	135.1
55°	116.8
57.5°	102.6
60°	90.8
62.5°	80.6
65°	71.2
67.5°	62.3
70°	54.1
72.5°	46.4
75°	39.1
77.5°	32.2
80°	25.2
82.5°	18.7
85°	12.2
87.5°	6.1
90°	0.0



TEST NUMBER: P866543  
 CATALOG NUMBER: PRLX-2004-M-935-15L-G-U-S-X-X-WHHR-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.46	13.93	12.83	14.25	14.56	12.46	13.93	12.83	14.25	14.56
	3H	14.04	15.36	14.42	15.69	16.05	14.04	15.36	14.42	15.69	16.05
	4H	14.68	15.92	15.08	16.27	16.65	14.68	15.92	15.08	16.27	16.65
	6H	15.20	16.35	15.62	16.72	17.11	15.20	16.35	15.62	16.72	17.11
	8H	15.39	16.48	15.82	16.87	17.27	15.39	16.48	15.82	16.87	17.27
	12H	15.54	16.58	15.97	16.96	17.39	15.54	16.58	15.97	16.96	17.39
4H	2H	12.99	14.22	13.39	14.57	14.95	12.99	14.22	13.39	14.57	14.95
	3H	14.81	15.83	15.22	16.24	16.64	14.81	15.83	15.22	16.24	16.64
	4H	15.59	16.51	16.02	16.93	17.37	15.59	16.51	16.02	16.93	17.37
	6H	16.25	17.06	16.71	17.50	17.96	16.25	17.06	16.71	17.50	17.96
	8H	16.50	17.25	16.96	17.70	18.16	16.50	17.25	16.96	17.70	18.16
	12H	16.69	17.37	17.18	17.84	18.32	16.69	17.37	17.18	17.84	18.32
8H	4H	15.88	16.63	16.34	17.08	17.54	15.88	16.63	16.34	17.08	17.54
	6H	16.68	17.31	17.18	17.80	18.28	16.68	17.31	17.18	17.80	18.28
	8H	17.02	17.58	17.53	18.09	18.58	17.02	17.58	17.53	18.09	18.58
	12H	17.31	17.80	17.82	18.30	18.86	17.31	17.80	17.82	18.30	18.86
12H	4H	15.91	16.58	16.39	17.06	17.53	15.91	16.58	16.39	17.06	17.53
	6H	16.75	17.31	17.26	17.82	18.31	16.75	17.31	17.26	17.82	18.31
	8H	17.15	17.64	17.66	18.14	18.70	17.15	17.64	17.66	18.14	18.70