

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219757

Luminaire Tested: **MRZ-1-REC-X-4-L35-97-FL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219757  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14876)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-4-L35-97-FL-UNV-X-STD-HEX  
Description: MRZ INTEGRAL LED DOWNLIGHT  
40 DEGREE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 4  
Light Source: (1) 3500K CCT, 97 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 749.7 lumens  
Efficiency: N/A  
Efficacy: 47.4 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 15.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219757

CATALOG NUMBER: MRZ-1-REC-X-4-L35-97-FL-UNV-X-STD-HEX

### Luminous Intensity Polar Plot





TEST NUMBER: P219757

CATALOG NUMBER: MRZ-1-REC-X-4-L35-97-FL-UNV-X-STD-HEX

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81
6	95	88	84	80	94	88	83	80	86	83	80	85	82	79	84	81	79	78
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	75
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69
10	83	76	71	68	83	75	71	68	75	71	68	74	70	68	73	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1024601
5°	973491
10°	841965
15°	631533
20°	393625
25°	206866
30°	93261
35°	36078
40°	14105
45°	7117
50°	3377
55°	2495
60°	1480
65°	1751
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219757

CATALOG NUMBER: MRZ-1-REC-X-4-L35-97-FL-UNV-X-STD-HEX

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	179.0	23.9
10°-20°	334.1	44.6
20°-30°	181.3	24.2
30°-40°	43.9	5.9
40°-50°	8.3	1.1
50°-60°	2.3	0.3
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	694.4	92.6
0°-40°	738.2	98.5
0°-60°	748.8	99.9
0°-90°	749.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	749.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2077	
5°	1966	179
15°	1236	334
25°	380	181
35°	60	44
45°	10	8
55°	3	2
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P219757

CATALOG NUMBER: MRZ-1-REC-X-4-L35-97-FL-UNV-X-STD-HEX

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2076.7
2.5°	2038.7
5°	1965.6
7.5°	1856.0
10°	1680.6
12.5°	1473.1
15°	1236.4
17.5°	983.5
20°	749.7
22.5°	542.2
25°	380.0
27.5°	255.7
30°	163.7
32.5°	100.8
35°	59.9
37.5°	36.5
40°	21.9
42.5°	14.6
45°	10.2
47.5°	5.8
50°	4.4
52.5°	2.9
55°	2.9
57.5°	1.5
60°	1.5
62.5°	1.5
65°	1.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)