

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866551

Luminaire Tested: PRLX-2004-M-935-25L-G-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-42)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-M-935-25L-G-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1530.1 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.2
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 21.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866551

CATALOG NUMBER: PRLX-2004-M-935-25L-G-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P866551

CATALOG NUMBER: PRLX-2004-M-935-25L-G-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	94	84	77	71	91	83	76	70	80	74	69	77	72	68	75	70	67	65
4	87	76	68	62	84	74	67	61	72	66	60	70	64	60	68	63	59	57
5	80	69	60	54	78	67	60	54	65	59	53	64	58	53	62	57	52	50
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37
9	61	49	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5797
5°	5813
10°	5825
15°	5817
20°	5795
25°	5729
30°	5428
35°	4922
40°	4354
45°	3778
50°	3216
55°	2701
60°	2407
65°	2235
70°	2098
75°	2001
80°	1929
85°	1862

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3778 cd/sqm

TEST NUMBER: P866551

CATALOG NUMBER: PRLX-2004-M-935-25L-G-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	4.5
10°-20°	199.4	13.0
20°-30°	298.0	19.5
30°-40°	316.3	20.7
40°-50°	259.8	17.0
50°-60°	177.7	11.6
60°-70°	118.1	7.7
70°-80°	69.1	4.5
80°-90°	22.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	566.6	37.0
0°-40°	882.9	57.7
0°-60°	1320.3	86.3
0°-90°	1530.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1530.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	729	
5°	728	69
15°	706	199
25°	653	298
35°	507	316
45°	336	260
55°	195	178
65°	119	118
75°	65	69
85°	20	23
90°	0	

TEST NUMBER: P866551

CATALOG NUMBER: PRLX-2004-M-935-25L-G-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	728.6
2.5°	728.6
5°	727.9
7.5°	725.2
10°	721.1
12.5°	715.0
15°	706.2
17.5°	696.7
20°	684.5
22.5°	670.9
25°	652.6
27.5°	624.8
30°	590.9
32.5°	552.2
35°	506.8
37.5°	463.3
40°	419.2
42.5°	376.5
45°	335.8
47.5°	298.5
50°	259.8
52.5°	225.2
55°	194.7
57.5°	171.0
60°	151.3
62.5°	134.3
65°	118.7
67.5°	103.8
70°	90.2
72.5°	77.3
75°	65.1
77.5°	53.6
80°	42.1
82.5°	31.2
85°	20.4
87.5°	10.2
90°	0.0



TEST NUMBER: P866551
 CATALOG NUMBER: PRLX-2004-M-935-25L-G-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.24	15.71	14.60	16.02	16.34	14.24	15.71	14.60	16.02	16.34
	3H	15.82	17.14	16.20	17.47	17.83	15.82	17.14	16.20	17.47	17.83
	4H	16.46	17.69	16.86	18.04	18.42	16.46	17.69	16.86	18.04	18.42
	6H	16.98	18.12	17.39	18.49	18.88	16.98	18.12	17.39	18.49	18.88
	8H	17.17	18.26	17.60	18.65	19.05	17.17	18.26	17.60	18.65	19.05
	12H	17.31	18.35	17.74	18.73	19.16	17.31	18.35	17.74	18.73	19.16
4H	2H	14.76	16.00	15.16	16.35	16.73	14.76	16.00	15.16	16.35	16.73
	3H	16.58	17.61	16.99	18.01	18.41	16.58	17.61	16.99	18.01	18.41
	4H	17.36	18.28	17.79	18.70	19.14	17.36	18.28	17.79	18.70	19.14
	6H	18.03	18.83	18.48	19.27	19.74	18.03	18.83	18.48	19.27	19.74
	8H	18.27	19.03	18.74	19.47	19.94	18.27	19.03	18.74	19.47	19.94
	12H	18.47	19.14	18.95	19.62	20.09	18.47	19.14	18.95	19.62	20.09
8H	4H	17.65	18.41	18.12	18.85	19.32	17.65	18.41	18.12	18.85	19.32
	6H	18.46	19.08	18.96	19.57	20.05	18.46	19.08	18.96	19.57	20.05
	8H	18.80	19.36	19.31	19.87	20.35	18.80	19.36	19.31	19.87	20.35
	12H	19.09	19.58	19.60	20.07	20.64	19.09	19.58	19.60	20.07	20.64
12H	4H	17.68	18.36	18.17	18.83	19.31	17.68	18.36	18.17	18.83	19.31
	6H	18.52	19.08	19.04	19.59	20.08	18.52	19.08	19.04	19.59	20.08
	8H	18.92	19.42	19.43	19.91	20.48	18.92	19.42	19.43	19.91	20.48