

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866560

Luminaire Tested: PRLX-2004-M-935-35L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866560  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-935-35L-L-U-S-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,  
BELL WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 4  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1511.2 lumens  
Efficiency: N/A  
Efficacy: 50.4 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 30  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866560

CATALOG NUMBER: PRLX-2004-M-935-35L-L-U-S-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866560

CATALOG NUMBER: PRLX-2004-M-935-35L-L-U-S-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	81
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78	74	71	70
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69	65	62	60
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65	61	58	56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51		59	54	51		58	54	51	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	12097
5°	11810
10°	11294
15°	10873
20°	10509
25°	10121
30°	9711
35°	7176
40°	1815
45°	214
50°	141
55°	132
60°	121
65°	107
70°	88
75°	86
80°	87
85°	82

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 214 cd/sqm

TEST NUMBER: P866560

CATALOG NUMBER: PRLX-2004-M-935-35L-L-U-S-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.6	9.2
10°-20°	371.9	24.6
20°-30°	530.8	35.1
30°-40°	416.0	27.5
40°-50°	36.2	2.4
50°-60°	8.5	0.6
60°-70°	5.6	0.4
70°-80°	3.0	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1041.3	68.9
0°-40°	1457.3	96.4
0°-60°	1501.9	99.4
0°-90°	1511.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1511.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1520	
5°	1479	139
15°	1320	372
25°	1153	531
35°	739	416
45°	19	36
55°	10	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P866560

CATALOG NUMBER: PRLX-2004-M-935-35L-L-U-S-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1520.5
2.5°	1512.0
5°	1478.8
7.5°	1438.9
10°	1398.0
12.5°	1359.1
15°	1320.1
17.5°	1281.2
20°	1241.3
22.5°	1197.6
25°	1153.0
27.5°	1108.4
30°	1057.1
32.5°	961.1
35°	738.9
37.5°	408.4
40°	174.8
42.5°	69.3
45°	19.0
47.5°	13.3
50°	11.4
52.5°	10.4
55°	9.5
57.5°	8.5
60°	7.6
62.5°	6.6
65°	5.7
67.5°	4.7
70°	3.8
72.5°	3.8
75°	2.8
77.5°	1.9
80°	1.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0



TEST NUMBER: P866560  
 CATALOG NUMBER: PRLX-2004-M-935-35L-L-U-S-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00