

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219917

Luminaire Tested: **MRZ-1-REC-X-1H-L40-80-WFL-UNV-X-STD-SFL**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219917
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14883)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-1H-L40-80-WFL-UNV-X-STD-SFL
Description: MRZ INTEGRAL LED DOWNLIGHT
55 DEGREE WIDE FLOOD OPTIC WITH SOFT FOCUS LENS, LIGHT LEVEL 1
Light Source: (1) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 621.8 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.9
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 6.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219917

CATALOG NUMBER: MRZ-1-REC-X-1H-L40-80-WFL-UNV-X-STD-SFL

Luminous Intensity Polar Plot





TEST NUMBER: P219917

CATALOG NUMBER: MRZ-1-REC-X-1H-L40-80-WFL-UNV-X-STD-SFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66
6	85	75	69	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	307918
5°	305826
10°	294282
15°	271329
20°	244250
25°	215086
30°	174501
35°	127568
40°	87077
45°	57424
50°	37534
55°	23827
60°	15295
65°	9456
70°	7068
75°	4575
80°	2273
85°	0



TEST NUMBER: P219917

CATALOG NUMBER: MRZ-1-REC-X-1H-L40-80-WFL-UNV-X-STD-SFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.9	9.3
10°-20°	148.2	23.8
20°-30°	179.1	28.8
30°-40°	133.3	21.4
40°-50°	65.6	10.6
50°-60°	26.0	4.2
60°-70°	8.9	1.4
70°-80°	2.7	0.4
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.2	62.0
0°-40°	518.5	83.4
0°-60°	610.1	98.1
0°-90°	621.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	621.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	624	
5°	618	58
15°	531	148
25°	395	179
35°	212	133
45°	82	66
55°	28	26
65°	8	9
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P219917

CATALOG NUMBER: MRZ-1-REC-X-1H-L40-80-WFL-UNV-X-STD-SFL

CANDELA DISTRIBUTION (FULL):

	0°
0°	624.1
2.5°	621.6
5°	617.5
7.5°	605.3
10°	587.4
12.5°	561.3
15°	531.2
17.5°	497.8
20°	465.2
22.5°	432.6
25°	395.1
27.5°	352.8
30°	306.3
32.5°	258.3
35°	211.8
37.5°	171.1
40°	135.2
42.5°	105.9
45°	82.3
47.5°	63.5
50°	48.9
52.5°	36.7
55°	27.7
57.5°	20.4
60°	15.5
62.5°	11.4
65°	8.1
67.5°	6.5
70°	4.9
72.5°	3.3
75°	2.4
77.5°	1.6
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)