

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866563

Luminaire Tested: PRLX-2004-M-935-35L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-54)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-M-935-35L-L-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 4
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3376.5 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 30
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866563

CATALOG NUMBER: PRLX-2004-M-935-35L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P866563

CATALOG NUMBER: PRLX-2004-M-935-35L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	51	50
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44	54	48	43	52	47	43	42
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	17348
5°	16853
10°	16297
15°	15895
20°	15576
25°	15215
30°	14780
35°	12287
40°	6915
45°	5204
50°	4995
55°	4730
60°	4458
65°	4237
70°	4087
75°	3971
80°	3871
85°	3816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5204 cd/sqm

TEST NUMBER: P866563

CATALOG NUMBER: PRLX-2004-M-935-35L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.6	5.9
10°-20°	544.4	16.1
20°-30°	798.0	23.6
30°-40°	745.5	22.1
40°-50°	378.1	11.2
50°-60°	305.3	9.0
60°-70°	224.4	6.6
70°-80°	136.6	4.0
80°-90°	45.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1541.1	45.6
0°-40°	2286.6	67.7
0°-60°	2969.9	88.0
0°-90°	3376.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3376.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2181	
5°	2110	199
15°	1930	544
25°	1733	798
35°	1265	746
45°	462	378
55°	341	305
65°	225	224
75°	129	137
85°	42	46
90°	0	

TEST NUMBER: P866563

CATALOG NUMBER: PRLX-2004-M-935-35L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	2180.6
2.5°	2162.6
5°	2110.3
7.5°	2062.8
10°	2017.3
12.5°	1973.6
15°	1929.9
17.5°	1886.2
20°	1839.7
22.5°	1789.3
25°	1733.3
27.5°	1676.3
30°	1608.9
32.5°	1502.5
35°	1265.1
37.5°	922.2
40°	665.8
42.5°	536.6
45°	462.5
47.5°	432.1
50°	403.6
52.5°	372.3
55°	341.0
57.5°	310.6
60°	280.2
62.5°	253.6
65°	225.1
67.5°	200.4
70°	175.7
72.5°	152.0
75°	129.2
77.5°	106.4
80°	84.5
82.5°	62.7
85°	41.8
87.5°	20.9
90°	0.0



TEST NUMBER: P866563
 CATALOG NUMBER: PRLX-2004-M-935-35L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.80	17.15	16.16	17.46	17.78	15.80	17.15	16.16	17.46	17.78
	3H	17.54	18.75	17.92	19.08	19.44	17.54	18.75	17.92	19.08	19.44
	4H	18.25	19.38	18.65	19.73	20.11	18.25	19.38	18.65	19.73	20.11
	6H	18.82	19.87	19.23	20.24	20.63	18.82	19.87	19.23	20.24	20.63
	8H	19.03	20.02	19.46	20.41	20.82	19.03	20.02	19.46	20.41	20.82
	12H	19.19	20.14	19.62	20.52	20.95	19.19	20.14	19.62	20.52	20.95
4H	2H	16.35	17.48	16.75	17.83	18.22	16.35	17.48	16.75	17.83	18.22
	3H	18.33	19.27	18.74	19.67	20.07	18.33	19.27	18.74	19.67	20.07
	4H	19.17	20.02	19.61	20.44	20.88	19.17	20.02	19.61	20.44	20.88
	6H	19.90	20.63	20.36	21.08	21.54	19.90	20.63	20.36	21.08	21.54
	8H	20.16	20.85	20.63	21.30	21.77	20.16	20.85	20.63	21.30	21.77
	12H	20.38	20.99	20.86	21.47	21.94	20.38	20.99	20.86	21.47	21.94
8H	4H	19.48	20.17	19.95	20.62	21.09	19.48	20.17	19.95	20.62	21.09
	6H	20.35	20.92	20.85	21.41	21.89	20.35	20.92	20.85	21.41	21.89
	8H	20.72	21.22	21.24	21.74	22.23	20.72	21.22	21.24	21.74	22.23
	12H	21.03	21.48	21.55	21.97	22.54	21.03	21.48	21.55	21.97	22.54
12H	4H	19.51	20.13	20.00	20.61	21.08	19.51	20.13	20.00	20.61	21.08
	6H	20.42	20.93	20.94	21.44	21.93	20.42	20.93	20.94	21.44	21.93
	8H	20.85	21.30	21.37	21.79	22.36	20.85	21.30	21.37	21.79	22.36