

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866573

Luminaire Tested: PRLX-2004-M-935-55L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-43)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Pentalux
Catalog Number: PRLX-2004-M-935-55L-G-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
BELL WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 6
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1112.8 lumens
Efficiency: N/A
Efficacy: 23.0 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 48.3
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866573

CATALOG NUMBER: PRLX-2004-M-935-55L-G-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866573

CATALOG NUMBER: PRLX-2004-M-935-55L-G-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	75	81	77	74	72
4	91	82	75	70	89	81	74	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5545
5°	5542
10°	5522
15°	5482
20°	5383
25°	5254
30°	5004
35°	4392
40°	3595
45°	2670
50°	1718
55°	932
60°	689
65°	589
70°	521
75°	458
80°	412
85°	411

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2670 cd/sqm

TEST NUMBER: P866573

CATALOG NUMBER: PRLX-2004-M-935-55L-G-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	5.9
10°-20°	187.4	16.8
20°-30°	274.5	24.7
30°-40°	280.3	25.2
40°-50°	183.2	16.5
50°-60°	68.1	6.1
60°-70°	31.7	2.9
70°-80°	16.3	1.5
80°-90°	5.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.8	47.4
0°-40°	808.1	72.6
0°-60°	1059.4	95.2
0°-90°	1112.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1112.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	697	
5°	694	66
15°	666	187
25°	598	275
35°	452	280
45°	237	183
55°	67	68
65°	31	32
75°	15	16
85°	4	5
90°	0	

TEST NUMBER: P866573

CATALOG NUMBER: PRLX-2004-M-935-55L-G-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	697.0
2.5°	695.5
5°	694.0
7.5°	689.5
10°	683.5
12.5°	676.1
15°	665.6
17.5°	652.2
20°	635.8
22.5°	617.9
25°	598.5
27.5°	576.1
30°	544.7
32.5°	503.0
35°	452.2
37.5°	400.0
40°	346.2
42.5°	291.0
45°	237.3
47.5°	186.6
50°	138.8
52.5°	98.5
55°	67.2
57.5°	50.7
60°	43.3
62.5°	37.3
65°	31.3
67.5°	26.9
70°	22.4
72.5°	19.4
75°	14.9
77.5°	11.9
80°	9.0
82.5°	7.5
85°	4.5
87.5°	3.0
90°	0.0



TEST NUMBER: P866573
 CATALOG NUMBER: PRLX-2004-M-935-55L-G-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.15	8.41	7.52	8.72	9.04	7.15	8.41	7.52	8.72	9.04
	3H	8.35	9.46	8.73	9.79	10.15	8.35	9.46	8.73	9.79	10.15
	4H	8.79	9.82	9.19	10.17	10.55	8.79	9.82	9.19	10.17	10.55
	6H	9.09	10.04	9.51	10.41	10.81	9.09	10.04	9.51	10.41	10.81
	8H	9.22	10.12	9.65	10.51	10.92	9.22	10.12	9.65	10.51	10.92
	12H	9.31	10.17	9.75	10.55	10.98	9.31	10.17	9.75	10.55	10.98
4H	2H	7.52	8.55	7.92	8.90	9.29	7.52	8.55	7.92	8.90	9.29
	3H	8.94	9.78	9.35	10.18	10.59	8.94	9.78	9.35	10.18	10.59
	4H	9.48	10.23	9.91	10.65	11.09	9.48	10.23	9.91	10.65	11.09
	6H	9.90	10.55	10.37	11.00	11.46	9.90	10.55	10.37	11.00	11.46
	8H	10.08	10.69	10.55	11.13	11.61	10.08	10.69	10.55	11.13	11.61
	12H	10.22	10.75	10.71	11.24	11.71	10.22	10.75	10.71	11.24	11.71
8H	4H	9.64	10.25	10.11	10.69	11.17	9.64	10.25	10.11	10.69	11.17
	6H	10.18	10.67	10.68	11.17	11.65	10.18	10.67	10.68	11.17	11.65
	8H	10.44	10.89	10.97	11.40	11.90	10.44	10.89	10.97	11.40	11.90
	12H	10.67	11.06	11.18	11.55	12.13	10.67	11.06	11.18	11.55	12.13
12H	4H	9.64	10.17	10.12	10.65	11.13	9.64	10.17	10.12	10.65	11.13
	6H	10.20	10.65	10.73	11.16	11.66	10.20	10.65	10.73	11.16	11.66
	8H	10.53	10.92	11.05	11.42	11.99	10.53	10.92	11.05	11.42	11.99