

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866579

Luminaire Tested: PRLX-2004-M-935-55L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866579  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-54)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-935-55L-L-U-S-X-X-WHHR-X  
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,  
BELL WITH WHITE INTERIOR SHADE.  
LIGHT LEVEL 6  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5305.9 lumens  
Efficiency: N/A  
Efficacy: 109.9 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 48.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866579

CATALOG NUMBER: PRLX-2004-M-935-55L-L-U-S-X-X-WHHR-X

### Luminous Intensity Polar Plot



TEST NUMBER: P866579

CATALOG NUMBER: PRLX-2004-M-935-55L-L-U-S-X-X-WHHR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	51	50
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44	54	48	43	52	47	43	42
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27262
5°	26484
10°	25609
15°	24979
20°	24475
25°	23909
30°	23225
35°	19308
40°	10865
45°	8177
50°	7851
55°	7432
60°	7006
65°	6658
70°	6422
75°	6240
80°	6084
85°	5997

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8177 cd/sqm

TEST NUMBER: P866579

CATALOG NUMBER: PRLX-2004-M-935-55L-L-U-S-X-X-WHHR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	312.1	5.9
10°-20°	855.5	16.1
20°-30°	1254.0	23.6
30°-40°	1171.5	22.1
40°-50°	594.1	11.2
50°-60°	479.7	9.0
60°-70°	352.6	6.6
70°-80°	214.6	4.0
80°-90°	71.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2421.7	45.6
0°-40°	3593.2	67.7
0°-60°	4667.0	88.0
0°-90°	5305.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5305.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3427	
5°	3316	312
15°	3033	856
25°	2724	1254
35°	1988	1172
45°	727	594
55°	536	480
65°	354	353
75°	203	215
85°	66	72
90°	0	

TEST NUMBER: P866579

CATALOG NUMBER: PRLX-2004-M-935-55L-L-U-S-X-X-WHHR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3426.7
2.5°	3398.3
5°	3316.2
7.5°	3241.6
10°	3170.0
12.5°	3101.3
15°	3032.7
17.5°	2964.0
20°	2890.9
22.5°	2811.8
25°	2723.7
27.5°	2634.2
30°	2528.2
32.5°	2361.1
35°	1988.0
37.5°	1449.2
40°	1046.2
42.5°	843.2
45°	726.8
47.5°	679.1
50°	634.3
52.5°	585.0
55°	535.8
57.5°	488.0
60°	440.3
62.5°	398.5
65°	353.7
67.5°	314.9
70°	276.1
72.5°	238.8
75°	203.0
77.5°	167.2
80°	132.8
82.5°	98.5
85°	65.7
87.5°	32.8
90°	0.0



TEST NUMBER: P866579  
 CATALOG NUMBER: PRLX-2004-M-935-55L-L-U-S-X-X-WHHR-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.37	18.72	17.73	19.03	19.35	17.37	18.72	17.73	19.03	19.35
	3H	19.11	20.32	19.49	20.65	21.01	19.11	20.32	19.49	20.65	21.01
	4H	19.82	20.95	20.22	21.30	21.68	19.82	20.95	20.22	21.30	21.68
	6H	20.39	21.44	20.80	21.81	22.20	20.39	21.44	20.80	21.81	22.20
	8H	20.60	21.59	21.03	21.98	22.39	20.60	21.59	21.03	21.98	22.39
	12H	20.76	21.71	21.19	22.09	22.52	20.76	21.71	21.19	22.09	22.52
4H	2H	17.92	19.05	18.32	19.40	19.79	17.92	19.05	18.32	19.40	19.79
	3H	19.90	20.84	20.31	21.24	21.64	19.90	20.84	20.31	21.24	21.64
	4H	20.74	21.59	21.18	22.01	22.45	20.74	21.59	21.18	22.01	22.45
	6H	21.47	22.20	21.93	22.65	23.11	21.47	22.20	21.93	22.65	23.11
	8H	21.73	22.42	22.20	22.87	23.34	21.73	22.42	22.20	22.87	23.34
	12H	21.95	22.56	22.43	23.04	23.51	21.95	22.56	22.43	23.04	23.51
8H	4H	21.05	21.74	21.52	22.19	22.66	21.05	21.74	21.52	22.19	22.66
	6H	21.92	22.49	22.42	22.98	23.46	21.92	22.49	22.42	22.98	23.46
	8H	22.29	22.79	22.81	23.31	23.80	22.29	22.79	22.81	23.31	23.80
	12H	22.60	23.05	23.12	23.54	24.11	22.60	23.05	23.12	23.54	24.11
12H	4H	21.08	21.69	21.57	22.18	22.65	21.08	21.69	21.57	22.18	22.65
	6H	21.99	22.50	22.51	23.01	23.50	21.99	22.50	22.51	23.01	23.50
	8H	22.42	22.87	22.94	23.36	23.93	22.42	22.87	22.94	23.36	23.93