

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219553

Luminaire Tested: **MRZ-1-REC-X-2-L40-80-NFL-UNV-X-STD**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14859)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-2-L40-80-NFL-UNV-X-STD
Description: MRZ INTEGRAL LED DOWNLIGHT
25 DEGREE NARROW FLOOD OPTIC, LIGHT LEVEL2
Light Source: (1) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 972.6 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.37
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 8.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219553

CATALOG NUMBER: MRZ-1-REC-X-2-L40-80-NFL-UNV-X-STD

Luminous Intensity Polar Plot





TEST NUMBER: P219553

CATALOG NUMBER: MRZ-1-REC-X-2-L40-80-NFL-UNV-X-STD

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	81	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77
10	89	83	79	76	89	83	79	76	82	78	76	81	78	76	81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2482044
5°	2250431
10°	1648059
15°	671988
20°	229287
25°	134027
30°	74859
35°	40234
40°	21512
45°	14025
50°	5987
55°	3871
60°	2171
65°	1284
70°	1587
75°	2097
80°	0
85°	0



TEST NUMBER: P219553

CATALOG NUMBER: MRZ-1-REC-X-2-L40-80-NFL-UNV-X-STD

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	393.2	40.4
10°-20°	397.5	40.9
20°-30°	116.1	11.9
30°-40°	44.5	4.6
40°-50°	14.9	1.5
50°-60°	4.1	0.4
60°-70°	1.5	0.2
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	906.9	93.2
0°-40°	951.4	97.8
0°-60°	970.4	99.8
0°-90°	972.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	972.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5031	
5°	4544	393
15°	1316	398
25°	246	116
35°	67	44
45°	20	15
55°	4	4
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P219553

CATALOG NUMBER: MRZ-1-REC-X-2-L40-80-NFL-UNV-X-STD

CANDELA DISTRIBUTION (FULL):

0°	
0°	5030.7
2.5°	4914.8
5°	4543.9
7.5°	3978.0
10°	3289.6
12.5°	2350.5
15°	1315.6
17.5°	698.5
20°	436.7
22.5°	324.2
25°	246.2
27.5°	183.8
30°	131.4
32.5°	94.7
35°	66.8
37.5°	46.8
40°	33.4
42.5°	25.6
45°	20.1
47.5°	12.3
50°	7.8
52.5°	5.6
55°	4.5
57.5°	3.3
60°	2.2
62.5°	2.2
65°	1.1
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)