

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866582

Luminaire Tested: PRLX-2004-M-935-65L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866582
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-M-935-65L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 7
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1297.5 lumens
Efficiency: N/A
Efficacy: 22.1 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 58.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866582

CATALOG NUMBER: PRLX-2004-M-935-65L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866582

CATALOG NUMBER: PRLX-2004-M-935-65L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56	65	60	56	64	59	55	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	46	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6497
5°	6508
10°	6483
15°	6421
20°	6302
25°	6162
30°	5882
35°	5139
40°	4177
45°	3115
50°	2009
55°	1028
60°	786
65°	665
70°	616
75°	541
80°	486
85°	484

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3115 cd/sqm

TEST NUMBER: P866582

CATALOG NUMBER: PRLX-2004-M-935-65L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	6.0
10°-20°	219.6	16.9
20°-30°	322.0	24.8
30°-40°	327.7	25.3
40°-50°	212.9	16.4
50°-60°	77.8	6.0
60°-70°	36.0	2.8
70°-80°	18.8	1.5
80°-90°	5.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.0	47.7
0°-40°	946.6	73.0
0°-60°	1237.3	95.4
0°-90°	1297.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1297.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	817	
5°	815	77
15°	780	220
25°	702	322
35°	529	328
45°	277	213
55°	74	78
65°	35	36
75°	18	19
85°	5	5
90°	0	

TEST NUMBER: P866582

CATALOG NUMBER: PRLX-2004-M-935-65L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	816.6
2.5°	816.6
5°	814.9
7.5°	809.6
10°	802.5
12.5°	793.7
15°	779.6
17.5°	763.7
20°	744.3
22.5°	724.9
25°	702.0
27.5°	675.5
30°	640.3
32.5°	587.4
35°	529.1
37.5°	467.4
40°	402.2
42.5°	338.7
45°	276.9
47.5°	215.2
50°	162.3
52.5°	112.9
55°	74.1
57.5°	58.2
60°	49.4
62.5°	42.3
65°	35.3
67.5°	30.0
70°	26.5
72.5°	21.2
75°	17.6
77.5°	14.1
80°	10.6
82.5°	7.1
85°	5.3
87.5°	1.8
90°	0.0

TEST NUMBER: P866582
 CATALOG NUMBER: PRLX-2004-M-935-65L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.58	8.83	7.94	9.14	9.46	7.58	8.83	7.94	9.14	9.46
	3H	8.76	9.87	9.14	10.20	10.57	8.76	9.87	9.14	10.20	10.57
	4H	9.20	10.23	9.61	10.58	10.97	9.20	10.23	9.61	10.58	10.97
	6H	9.54	10.48	9.95	10.85	11.24	9.54	10.48	9.95	10.85	11.24
	8H	9.63	10.52	10.06	10.91	11.32	9.63	10.52	10.06	10.91	11.32
	12H	9.70	10.55	10.13	10.94	11.37	9.70	10.55	10.13	10.94	11.37
4H	2H	7.93	8.96	8.33	9.31	9.69	7.93	8.96	8.33	9.31	9.69
	3H	9.34	10.18	9.76	10.59	10.99	9.34	10.18	9.76	10.59	10.99
	4H	9.90	10.65	10.34	11.07	11.51	9.90	10.65	10.34	11.07	11.51
	6H	10.35	11.00	10.82	11.44	11.91	10.35	11.00	10.82	11.44	11.91
	8H	10.48	11.08	10.95	11.53	12.00	10.48	11.08	10.95	11.53	12.00
	12H	10.59	11.12	11.08	11.61	12.08	10.59	11.12	11.08	11.61	12.08
8H	4H	10.07	10.68	10.55	11.12	11.60	10.07	10.68	10.55	11.12	11.60
	6H	10.63	11.12	11.14	11.62	12.10	10.63	11.12	11.14	11.62	12.10
	8H	10.82	11.26	11.35	11.78	12.27	10.82	11.26	11.35	11.78	12.27
	12H	11.02	11.41	11.53	11.90	12.47	11.02	11.41	11.53	11.90	12.47
12H	4H	10.07	10.60	10.56	11.08	11.56	10.07	10.60	10.56	11.08	11.56
	6H	10.65	11.09	11.17	11.60	12.10	10.65	11.09	11.17	11.60	12.10
	8H	10.89	11.28	11.40	11.77	12.35	10.89	11.28	11.40	11.77	12.35