

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: RSA

Report Number: P219716

Luminaire Tested: **MRZ-1-REC-X-3-L40-80-FL-UNV-X-STD**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P219716  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14875)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: RSA  
Catalog Number: MRZ-1-REC-X-3-L40-80-FL-UNV-X-STD  
Description: MRZ INTEGRAL LED DOWNLIGHT  
40 DEGREE FLOOD OPTIC, LIGHT LEVEL 3  
Light Source: (1) 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1336.3 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.66  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 12  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P219716

CATALOG NUMBER: MRZ-1-REC-X-3-L40-80-FL-UNV-X-STD

### Luminous Intensity Polar Plot





TEST NUMBER: P219716

CATALOG NUMBER: MRZ-1-REC-X-3-L40-80-FL-UNV-X-STD

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	102	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1206412
5°	1229890
10°	1190705
15°	1014928
20°	724245
25°	445088
30°	240302
35°	115522
40°	55905
45°	29724
50°	17500
55°	11784
60°	7499
65°	5370
70°	4328
75°	2859
80°	4262
85°	0



TEST NUMBER: P219716

CATALOG NUMBER: MRZ-1-REC-X-3-L40-80-FL-UNV-X-STD

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	234.1	17.5
10°-20°	535.6	40.1
20°-30°	379.9	28.4
30°-40°	131.1	9.8
40°-50°	35.6	2.7
50°-60°	12.5	0.9
60°-70°	5.1	0.4
70°-80°	2.2	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1149.6	86.0
0°-40°	1280.7	95.8
0°-60°	1328.8	99.4
0°-90°	1336.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1336.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2445	
5°	2483	234
15°	1987	536
25°	818	380
35°	192	131
45°	43	36
55°	14	13
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P219716

CATALOG NUMBER: MRZ-1-REC-X-3-L40-80-FL-UNV-X-STD

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2445.2
2.5°	2455.9
5°	2483.3
7.5°	2475.7
10°	2376.7
12.5°	2213.8
15°	1987.0
17.5°	1687.0
20°	1379.4
22.5°	1084.1
25°	817.6
27.5°	593.8
30°	421.8
32.5°	286.2
35°	191.8
37.5°	127.9
40°	86.8
42.5°	59.4
45°	42.6
47.5°	30.5
50°	22.8
52.5°	16.7
55°	13.7
57.5°	10.7
60°	7.6
62.5°	6.1
65°	4.6
67.5°	4.6
70°	3.0
72.5°	3.0
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)