

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: RSA

Report Number: P219878

Luminaire Tested: **MRZ-1-REC-X-4-L40-80-WFL-UNV-X-STD-HEX**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P219878
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14881)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: RSA
Catalog Number: MRZ-1-REC-X-4-L40-80-WFL-UNV-X-STD-HEX
Description: MRZ INTEGRAL LED DOWNLIGHT
55 DEGREE WIDE FLOOD OPTIC WITH HEX LOUVER, LIGHT LEVEL 4
Light Source: (1) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 738.3 lumens
Efficiency: N/A
Efficacy: 46.7 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.67
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 15.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P219878

CATALOG NUMBER: MRZ-1-REC-X-4-L40-80-WFL-UNV-X-STD-HEX

Luminous Intensity Polar Plot





TEST NUMBER: P219878

CATALOG NUMBER: MRZ-1-REC-X-4-L40-80-WFL-UNV-X-STD-HEX

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	104	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	81	78	84	80	78	83	79	77	76
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	60	68	63	60	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	713772
5°	675045
10°	597031
15°	483355
20°	368056
25°	272410
30°	175298
35°	92635
40°	40125
45°	14932
50°	5987
55°	3355
60°	1875
65°	2218
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P219878

CATALOG NUMBER: MRZ-1-REC-X-4-L40-80-WFL-UNV-X-STD-HEX

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	16.9
10°-20°	260.6	35.3
20°-30°	227.2	30.8
30°-40°	100.7	13.6
40°-50°	19.8	2.7
50°-60°	4.1	0.6
60°-70°	1.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	612.6	83.0
0°-40°	713.2	96.6
0°-60°	737.1	99.8
0°-90°	738.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	738.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1447	
5°	1363	125
15°	946	261
25°	500	227
35°	154	101
45°	21	20
55°	4	4
65°	2	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P219878

CATALOG NUMBER: MRZ-1-REC-X-4-L40-80-WFL-UNV-X-STD-HEX

CANDELA DISTRIBUTION (FULL):

0°	
0°	1446.7
2.5°	1417.5
5°	1363.0
7.5°	1289.0
10°	1191.7
12.5°	1072.9
15°	946.3
17.5°	813.9
20°	701.0
22.5°	601.7
25°	500.4
27.5°	403.1
30°	307.7
32.5°	222.0
35°	153.8
37.5°	99.3
40°	62.3
42.5°	35.0
45°	21.4
47.5°	13.6
50°	7.8
52.5°	5.8
55°	3.9
57.5°	3.9
60°	1.9
62.5°	1.9
65°	1.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)